



| | |
|--|--------------------------------------|
| Item #: F533-BN | UPC Code: 706411051081 |
| Product Family Name: Mojo II | Finish: Brushed Nickel |
| Category: Interior Fan | Category Type: Ceiling Fan |
| Certification 4000048 | |
| Patents | |
| Notes: | |

Image File Name:
F533-BN--
1422960545.jpg



MEASUREMENTS

| | | | |
|--|---------------------------|-------------------|------------------------|
| Blade Finish: | Reversible Blades: | | |
| | No | | |
| Blade Material: PLYWOOD CONSTRUCTION | Slope: | | |
| | No | | |
| Blade Sweep: | No. of Blades: | Blade Pitch: | Hanging Weight: |
| 52 | 4 | 14 DEGREES | 18.25 |
| Downrod 1: | Downrod 1 Outside Dia: | Downrod 2: | Downrod 2 Outside Dia: |
| | | | |
| Ceiling to Lowest Point: (Dim A) | Ceiling to Blade: (Dim B) | Lead Wire: | Motor Size: |
| 13.50 | 8.00 | 18 | 153x15mm |

| | Low: | Low/Med: | Medium: | Med/High: | High: |
|------------------|---------|----------|---------|-----------|---------|
| RPM: | 84 | | 133 | | 168 |
| Amps: | 0.27 | | 0.42 | | 0.53 |
| Watts: | 14.000 | | 34.700 | | 62.600 |
| CFM: | 2641.00 | | 4090.00 | | 5138.00 |
| CFM/Watts | 188.64 | | 117.87 | | 82.08 |



FAN CONTROLS

| | | |
|-----------------------------------|---|--|
| Pull Chain Control: Yes | Works with Remote Control: Yes | Works with Wall Control: Yes |
| | Included Remote Control: | Included Wall Control: |
| | Compatible Remote Control[s]: RCS223,RCS213 | Compatible Wall Control[s]: WC106,WCS213,WC S223 |

LAMPING

| | | | | |
|--------------------------------|--|----------|-------------------|-------------------|
| No. of Bulbs: 3 | Light Type: B10.5,60w Candelabra Bulbs | | | |
| Max Bulb Wattage: 60 | Socket: E12 | | | |
| Light Kit: Yes | Dimmable: No | Ballast: | Rated Life Hours: | Uplight |
| Lamp Included: Yes | Color Temp.: | CRI: | Initial Lumens: | Delivered Lumens: |

GLASS

| | | |
|---------------------------|---------------------------|-------------------------|
| Description: | Material: Glass | |
| Part No.: GF533 | Quantity: 1 | |
| Width: 11.50 | Height: 4.13 | Length: 11.50 |



SHIPPING

| | | | |
|---------------------------------|------------------------------------|--|--------------------------|
| Carton Width: 14.000 | Carton Height: 11.750 | Carton Length: 25.130 | |
| Carton Weight: 21.890 | Carton Cubic Feet: 2.392 | Small Package Shippable: Yes | |
| Master Pack Width: | Master Pack Height: | Master Pack Length: | |
| Master Pack Weight: | Master Cubic Feet: | Multi-Pack: | Master Pack: 1 |



ETL Intertek

Yes