

Accent 1-Lt 120V

15251AZT (Textured Architectural Bronze)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____



Ordering Information

Product ID	15251AZT
Finish	Textured Architectural Bronze
Available Finishes	AZT, BKT

Dimensions

Weight	4.00 LBS
--------	----------

Specifications

Material	Aluminum
Glass Description	Tempered Convex Clear Glass

Electrical

Voltage	120V
Lead Wire Length	8.00"

Qualifications

Safety Rated	Wet
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	1
Max or Nominal Watt	150W
Socket Wire	150
Socket Type	Medium
Lamp Type	R40

Dimensions

Height	7.75"
Length	9.75"
Width	6.50"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Alternate	INCA	150W		

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.