







LAA4/0-38-5

One-hole, aluminum, long barrel, 4/0 AWG, 3/8" (9.5mm) stud hole.

Specs Packaging Details Documents [★ Add to Favorites](#) [Add to BOM](#)

| | |
|-----------------------------------|---|
| Product Type | Compression Connectors - Lugs |
| Material | Tin-Plated Aluminum |
| CSA Certified | Yes |
| UL Listed | Yes |
| Length (In.) | 3.56 |
| Length (mm) | 90.4 |
| Aluminum or Copper Conductor Size | 4/0 AWG |
| Stud Hole Size (In.) | 3/8 |
| Tongue Width (In.) | 1.19 |
| Barrel Length (In.) | 1.44 |
| Angle | Straight |
| Conductor Material | Aluminum or Copper |
| Panduit Color Code | White |
| Panduit Die Index No. | P66 |
| Part Features | dual rated,prefilled joint compound,enclosed barrel,tin plated to inhibit corrosion |
| Stud Hole Size (mm) | 9.5 |
| Tongue Thickness | 0.32 |
| Tongue Thickness (mm) | 8.1 |
| Tongue Width (mm) | 30.2 |
| Wire Strip Length (In.) | 1 3/4 |
| Wire Strip Length (mm) | 44.5 |
| RoHS Compliancy Status | Compliant |
| Min. Order Qty. | 1.0000 |
| Burndy Die Index No. | 298 |
| T&B Die Index No. | 66 |

[Back to Top](#)

Request a Quote
Are you looking for a free quote on Panduit
Products and Solutions?

Yes, I need a quote! ▶