


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number
Description
Status

YA2CN
 7818100802077
 CU HYLUG- 2STR-NEMA (1)
 Active

Web Use
 BURNDY Product Line

	Dimensional
Tongue Angle	Straight
Length (in)	2.88
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.12
B Length (in)	1.25
Pad Width (in)	0.83
Strip Length	1-5/16

Number of Holes
 Product Description

General

1
 Copper Compression Lug, 1 Hole
 w/o Inspection Window, 2 AWG,
 1/2" Stud, Long Barrel, Tin Plated

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

Conductor(s)

N/A
 N/A
 N/A
 N/A
 N/A
 2 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin
 1/2
 Brown
 Y
 10
 Copper

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Approvals / Certifications

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175

