



S5224

F120T12/CW/HO
 135 watt; T12; Fluorescent; 4200K Cool White; 62 CRI;
 Recessed Double Contact HO/VHO base

Features

- Professional grade fluorescent lamp
- Sustainable lighting product
- High lumen maintenance



S5224

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S5224	045923052248	135	T12	Recessed Double Contact HO/VHO	R17d	F120T12/CW/HO	1-1/2"
MOL In Inches	Nominal Length	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack	CRI
117"	120"	11500	12000	4200	Cool White	10	62
RoHS Compliant							
Yes							



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

