

Arlington resolves Lawsuit with Ply Gem Siding Group, Click to Learn More (<http://www.aifittings.com/about/press-releases/2016-10-27.pdf>)

Contact Us: 1-800-233-4717  (<http://www.facebook.com/aifittings>)  (<http://www.twitter.com/aifittings>) 

(<http://www.youtube.com/user/aifittings>)  (<http://www.aimedia.co>)

Arlington

Where Innovation Grows

(<http://www.aifittings.com/home>)

Search

Enter a Search Term Below

Track an Order

Enter a Purchase Order

Stay Informed

Would you like to learn about new and upcoming products, contests, and more? Simply enter your e-mail address below to stay informed.

How to Buy

Please enter your zip code to locate your Arlington sales representative who can provide you with a local distributor, pricing, and availability.

Buying Arlington products in Canada (<http://www.aifittings.com/locate/?canada>)?

Product Categories

- Conduit Bodies (<http://www.aifittings.com/catalog/conduit-bodies/>)
- Cord Grips (<http://www.aifittings.com/catalog/cord-grips/>)
- EMT Fittings (<http://www.aifittings.com/catalog/emt-fittings/>)
- Fan • Fixture Boxes (<http://www.aifittings.com/catalog/fan-and-fixture-boxes/>)
- Flex • AC • MC Fittings (<http://www.aifittings.com/catalog/flex-ac-mc-fittings/>)
- Floor Boxes (<http://www.aifittings.com/catalog/floor-boxes/>)
- GARD-N-POST™ (<http://www.aifittings.com/catalog/gard-n-post/>)
- Grounding (<http://www.aifittings.com/catalog/grounding/>)
- Home Theatre / Audio (<http://www.aifittings.com/catalog/home-theatre-audio-video/>)
- INBOX™ Weatherproof (<http://www.aifittings.com/catalog/inbox/>)
- Liquid Tight Fittings (<http://www.aifittings.com/catalog/liquid-tight-fittings/>)
- Low Voltage Cable Management (<http://www.aifittings.com/catalog/low-voltage-cable-management/>)
- Mast Parts (<http://www.aifittings.com/catalog/mast-parts/>)
- Miscellaneous (<http://www.aifittings.com/catalog/miscellaneous/>)
- NM Cable Fittings (<http://www.aifittings.com/catalog/non-metallic-fittings-and-supports/>)
- Rigid • IMC Fittings (<http://www.aifittings.com/catalog/rigid-imc-fittings/>)
- Siding Mounting Blocks (<http://www.aifittings.com/catalog/siding-mounting-blocks/>)
- Specialty Boxes (<http://www.aifittings.com/catalog/specialty-boxes/>)

Patents and Standards

- Arlington Patents (<http://www.aifittings.com/reference/patents>)
- UL/CSA Standards (<http://www.aifittings.com/reference/standards>)
- SNAP²IT® and SNAP-TITE® Notes (<http://www.aifittings.com/reference/notes>)

Catalog (/catalog/) / Fan • Fixture Boxes (/catalog/fan-fixture-boxes/)

/ ONE-BOX™ Side Mount Vapor Boxes for Fix... (/catalog/fan-fixture-boxes/one-box-side-mount-vapor-boxes-for-fixtures/) / FB443F



(<http://www.aimedia.co/media/images/FB443F.jpg>)

FB443F Product Information

Joist Mount Screw-On L-Shaped Vapor Box for Fans and Fixtures (Single Drywall)

[Specification Sheet \(http://www.aimedia.co/media/spec-sheets/VAPOR_BOXES.pdf\)](http://www.aimedia.co/media/spec-sheets/VAPOR_BOXES.pdf)

[Specification Sheet \(http://www.aimedia.co/media/spec-sheets/epage/VAPOR_BOXES\)](http://www.aimedia.co/media/spec-sheets/epage/VAPOR_BOXES)

[Catalog Page \(http://www.aimedia.co/media/catalog-pages/R-2-1.pdf\)](http://www.aimedia.co/media/catalog-pages/R-2-1.pdf)

[E-mail](#)

Additional Images



(<http://www.aimedia.co/media/images/FB443F-2.jpg>)



(<http://www.aimedia.co/media/images/FB443F-3.jpg>)





(<http://www.aimedia.co/media/images/FB443F-4.jpg>)




(<http://www.aimedia.co/media/images/FB443F-5.jpg>)

Basic Information

Part Number	FB443F
Description	Joist Mount Screw-On L-Shaped Vapor Box for Fans and Fixtures (Single Drywall)
UPC	018997762221
Unit Packaging	25pcs
Standard Packaging	25pcs
Country of Origin	 Made in USA
Listing	


Physical Information

Weight	0.38 lbs/each
Height	5.183"
Width	4.240"
Color	 Black
Material(s)	Non-Conductive Plastic


Technical Information

Line Drawing	FB443F Line Drawing (http://www.aimedia.co/media/line-drawings/FB442F-FB443FD.pdf)
Description/ Cu. In.	Fan or Fixture Single Drywall/ 18.8

Load Rating	UL rated: 70 lb fan; 200 lb fixture; CSA rated: 50 lb fan/fixture
Trade Size	N/A
Usage	Protects Against Air Infiltration

Follow Us On 

Facebook

(<http://www.facebook.com/aifittings>) 

Twitter

(<http://www.twitter.com/aifittings>) 

YouTube

(<http://www.youtube.com/user/aifittings>)

Contact Us **Arlington Industries, Inc.**

Arlington Industries, Inc. Copyright © 2016 Arlington Industries, Inc.

1 Stauffer Industrial Park Home (<http://www.aifittings.com/home>) | Contact Us (<http://www.aifittings.com/about/contact>) | Careers
Scranton, PA 18517 (<https://www.careers.aifittings.com/>) | Privacy Policy (<http://www.aifittings.com/policies/privacy-policy>) | Terms and
Conditions (<http://www.aifittings.com/policies/web-site-terms-and-conditions>)

Local 1-570-562-0270

Toll-Free 1-800-233-4717

Fax 1-570-562-0646

About Arlington

Arlington is a leading manufacturer of quality electrical products, communications products, home theater products, and more since 1949. To meet the changing needs of the electrical industry, Arlington continuously develops unique and innovative products that meet the quality standards our customers expect.

Stay Informed

Enter your e-mail address below to be notified about new product releases, contests, and more!

