

# Direct-Wire Fluorescent 13W WH

10042WH (White)

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_

Qty: \_\_\_\_\_

Comments: \_\_\_\_\_



## Dimensions

Height	1.00"
Length	21.00"
Width	3.50"

## Ordering Information

Product ID	10042WH
Finish	White

## Dimensions

Weight	1.00 LBS
--------	----------

## Photometrics

Kelvin Temperature	2700K
Color Rendering Index	85

## Specifications

Material	Steel
Glass Description	Frosted

## Electrical

Voltage	120V
Input Voltage	Single(120)
Operating Voltage Range	108-132

## Qualifications

Safety Rated	Dry
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

## Installation

Direct Wire	Yes
-------------	-----

## Primary Lamping

Light Source	Fluorescent
Lamp Included	Included
Number of Lights/LEDs	1
Lamp Type	FLUOR

### Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.