

MONORAIL


MonoRail

DESCRIPTION

Low-voltage conductor of two individual conductive metal pieces fused together by a plastic separator. Hand-bendable, field-cuttable MonoRail is rated for 300 watts at 12 volts, 600 watts at 24 volts. Each piece of rail is shipped with conductive connectors to join rail pieces end to end. Order additional connectors if cutting and rejoining rails. Standard


WEIGHT

0.27-1.1lb / 0.12-0.5kg ±



brown

COLOR OPTIONS



brown

clear

ORDERING INFORMATION

700MOA SHAPE OR SIZE	LENGTH (A)	COLOR	FINISH
STRAIGHT	24 24"	BR BROWN CLEAR	Z ANTIQUE BRONZE
	48 48"		C CHROME
	96 96"		S SATIN NICKEL



TECH LIGHTING®
 7400 Linder Avenue T 847.410.4400
 Skokie, Illinois 60077 F 847.410.4500
Tech Lighting, L.L.C.

700MOA _____

FIXTURE TYPE: _____

JOB NAME: _____

NOTES: _____



©2014 Tech Lighting, L.L.C. All Rights Reserved. The "Tech Lighting" graphic is a registered trademark of Tech Lighting, L.L.C. Tech Lighting reserves the right to change specifications for product improvements without notification.