

LED-8029M-A 24W LED for HID Retrofit for Post Top / Area




Models

LED-8029MXX-A, 120-277VAC, cULus, 3000K, 4000K or 5700K CCT, E26
 LED-8029MXXC-A, 347VAC, cUL, 3000K, 4000K or 5700K CCT, E26

Features

- > 24W LED Replaces 100W MH or HPS HID Lamps
- > UL approved for damp environments and enclosed fixtures
- > Advanced active cooling: Active cooling and dynamic temperature control
- > 50,000 hour rated LED life (supported by LM80 and ISTMT reports (see website))
- > 5 Year Limited Warranty - see website for details
- > Rated for enclosed fixture




Technical Specifications

Models US/CAN	LED-8029M30-A	LED-8029M40-A	LED-8029M57-A	LED-8029M30C-A	LED-8029M40C-A	LED-8029M57C-A
	USA			Canada		
CCT	3000K	4000K	5700K	3000K	4000K	5700K
Power Consumption	24 watts					
Replaces	100 MH/HPS					
Mounting	E39					
Voltage	120-277VAC			347VAC		
LED Type	2835					
Beam Angle	360°					
Dimmable	No					
Operating Temp	-40°F - +122°F					
Rated R70 Life	Up to 50,000 Hrs.					
Warranty	5 Year Limited*					
LM79 Specifications	Yes	Yes	Yes	Yes	Yes	Yes
Power (W)	23.22	22.43	22.14	22.64	22.52	22.14
CCT	2965	4026	5772	2948	4089	5746
Light Output	2362	2656	2667	2379	2712	2880
Efficacy	101	118	120	105	120	127
THD @ 277V	10%	10.61%	10.12%	16%	16.29%	17%
PF @ 277V	99	99	99	97	97	97
CRI:	82.6	84.4	85.2	81.9	84.7	84.8
R9	8	15	16	5	16	14
Duv	0.0002	-0.0009	0.0011	-0.0003	-0.0001	0.0019
Packaging	9/ Master Carton					
Unit	4.7"x 4.7"x 8.9" 1.2 lbs.					
Master	14.8"x 14.8" x 9.5" 12 lbs.					

DLC LISTED	MODEL	DLC CODE
	LED-8029M40-A	
	LED-8029M57-A	P17Z7EQS

Approved Categories:
 Replacement Lamps for Outdoor Pole/Arm-mounted
 Decorative Luminaires (Type B)

Photometric Data



Installation Notes:

- Ballast must be bypassed
- Installing surge/lightning protectors is highly recommended

LED Power Consumption (Watts)	HID Power Consumption (Watts)	HID Ballast Power Consumption (Watts)	Total Savings (Watts)	Annual Energy Savings (14 hrs/day)	Lifetime Energy Savings (over 50,000 hrs)
24	100	20	96	\$54	\$528

Mounting Orientation			Minimum Fixture Size Requirements (inches)	
Base Up	Base Down	Horiz	Length	Width
			8.9	4.9
Approved	Approved	Approved	Height	4.9
			Cu. Inches	213.7



188 S. Northwest Highway • Cary, IL 60013
 (847) 380-3540 • FAX: (847) 380-3542
 www.led-llc.com

