



Measurements:

| | | |
|-----------------------|-----------------|------------------|
| <u>Height</u> | <u>Width</u> | <u>Extension</u> |
| 8.00" | 6.00" | 2.62" |
| <u>BP Height</u> | <u>BP Width</u> | |
| 5.25" | 5.25" | |
| <u>Hanging Weight</u> | | |
| 1.98 lb | | |

Lamping:

| | |
|------------------------------|--------------------|
| Incandescent MB Incandescent | 1,150 Rated Lumens |
| 1.00 100W MB Incandescent | Color Temperature |
| 100 total watt | 2,500 Rated Life |
| Dimmable : Standard | |

Shipping:

| | | | |
|------------------------|---------------------|----------------------|----------------------|
| <u>Carton Weight</u> | <u>Carton Width</u> | <u>Carton Height</u> | <u>Carton Length</u> |
| 2.65 lb | 8.07" | 10.04" | 10.04" |
| <u>Master Pack Qty</u> | <u>UPC</u> | <u>UPS</u> | |
| 1.0000 | 783209212015 | Yes | |

Finish:

Oil Rubbed Bronze OI

Glass:

Wilshire WS

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB Incandescent (Not Included)
Lighting Direction: Both