



Measurements:

| | | |
|------------------|-----------------|------------------|
| <u>Height</u> | <u>Width</u> | <u>Extension</u> |
| 8.00" | 27.50" | 2.62" |
| <u>BP Height</u> | <u>BP Width</u> | |
| 5.25" | 5.25" | |

Hanging Weight
6.00 lb

Lamping:

| | |
|------------------------------|--------------------|
| Incandescent MB Incandescent | 4,600 Rated Lumens |
| 4.00 100W MB Incandescent | Color Temperature |
| 400 total watt | 2,500 Rated Life |
| Dimmable : Standard | |

Shipping:

| | | | |
|------------------------|---------------------|----------------------|----------------------|
| <u>Carton Weight</u> | <u>Carton Width</u> | <u>Carton Height</u> | <u>Carton Length</u> |
| 8.68 lb | 9.45" | 11.22" | 27.00" |
| <u>Master Pack Qty</u> | <u>UPC</u> | <u>UPS</u> | |
| 1.0000 | 783209212305 | Yes | |

Finish:

Satin Nickel SN

Glass:

Ice IC

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB Incandescent (Not Included)
Lighting Direction: Both