



**Measurements:**

<u>Height</u>	<u>Width</u>		
9.00"	13.00"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
6.92 lb	5.00"	1.00"	5.00"

**Lamping:**

Incandescent MB Incandescent 1,344 Rated Lumens  
 2.00 60W MB Incandescent Color Temperature  
 120 total watt 2,500 Rated Life  
 Dimmable : Standard

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
9.90 lb	16.14"	9.06"	16.14"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209054219	Yes	

**Finish:**

Satin Nickel SN

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Dry Location  
 Location

**Additional:**

MB Incandescent (Not Included)