



**Measurements:**

<u>Height</u>	<u>Width</u>
7.00"	6.00"
<u>Max OAH</u>	
7.00"	
<u>Hanging Weight</u>	
1.28 lb	

**Lamping:**

Incandescent MB Incandescent	672 Rated Lumens
1.00 60W MB Incandescent	Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
1.48 lb	6.50"	8.27"	6.50"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
8.82 lb	13.58"	8.66"	20.08"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
6.0000	783209588912	Yes	

**Finish:**

White WT

**Glass:**

White WT

**Material:**

Steel

**Certification:**

Dry Location  
Location

**Additional:**

MB Incandescent (Not Included)