



**Measurements:**

<u>Height</u>	<u>Width</u>	<u>Extension</u>
7.00"	29.50"	2.75"
<u>BP Height</u>	<u>BP Width</u>	
4.76"	6.50"	

Hanging Weight

9.65 lb

**Lamping:**

Incandescent MB Incandescent	4,600 Rated Lumens
4.00 100W MB Incandescent	Color Temperature
400 total watt	2,500 Rated Life
Dimmable : Standard	

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
12.98 lb	11.00"	9.25"	29.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209054301	Yes	

**Finish:**

Satin Nickel SN

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Damp Location  
Location

**Additional:**

MB Incandescent (Not Included)  
Lighting Direction: Both