



**Measurements:**

<u>Height</u>	<u>Width</u>
19.00"	17.00"
<u>Hanging Weight</u>	
4.84 lb	

**Lamping:**

Incandescent MB Incandescent	0 Rated Lumens
3.00 60W MB Incandescent	Color Temperature
180 total watt	
Dimmable : Standard Dimmer	

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
7.83 lb	7.00"	18.75"	17.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209108240	Yes	

**Finish:**

Satin Nickel SN

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Dry Location

**Additional:**

MB Incandescent (Not Included)