



Measurements:

<u>Height</u>	8.50"	<u>Width</u>	5.00"
<u>BP Height</u>	6.75"	<u>BP Width</u>	4.50"

Hanging Weight
1.50 lb

Lamping:

Incandescent MB Incandescent 0 Rated Lumens
 1.00 60W MB Incandescent Color Temperature
 60 total watt
 Dimmable : Standard Dimmer

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
2.02 lb	8.00"	6.25"	10.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209108288	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location

Additional:

MB Incandescent (Not Included)
 Lighting Direction: BOTH