



Measurements:

<u>Height</u>	<u>Width</u>		
22.00"	21.00"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
5.51 lb	4.75"	1.00"	4.75"

Lamping:

Incandescent MB Incandescent 0 Rated Lumens
 3.00 60W MB Incandescent Color Temperature
 180 total watt
 Dimmable : Standard Dimmer

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
11.07 lb	18.00"	9.00"	18.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209108356	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location

Additional:

MB Incandescent (Not Included)