



\*max overall height

**Measurements:**

Height

6.00"

Width

5.00"

Max OAH

50.50"

Hanging Weight

2.88 lb

**Lamping:**

Incandescent MB Incandescent

0 Rated Lumens

1.00 60W MB Incandescent

Color Temperature

60 total watt

Dimmable : Standard Dimmer

**Shipping:**

Carton Weight

Carton Width

Carton Height

Carton Length

3.32 lb

7.00"

6.25"

13.25"

Master Pack Qty

UPC

UPS

1.0000

783209108882

Yes

**Finish:**

Oil Rubbed Bronze OI

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Dry Location

**Additional:**

MB Incandescent (Not Included)

Slope: 120