



**Measurements:**

|                       |              |
|-----------------------|--------------|
| <u>Height</u>         | <u>Width</u> |
| 6.00"                 | 13.50"       |
| <u>Max OAH</u>        |              |
| 6.00"                 |              |
| <u>Hanging Weight</u> |              |
| 2.65 lb               |              |

**Lamping:**

|                              |                    |
|------------------------------|--------------------|
| Incandescent MB Incandescent | 1,344 Rated Lumens |
| 2.00 60W MB Incandescent     | Color Temperature  |
| 120 total watt               | 2,500 Rated Life   |
| Dimmable : Standard          |                    |

**Shipping:**

|                        |                     |                      |                      |
|------------------------|---------------------|----------------------|----------------------|
| <u>Carton Weight</u>   | <u>Carton Width</u> | <u>Carton Height</u> | <u>Carton Length</u> |
| 4.08 lb                | 13.58"              | 5.91"                | 13.58"               |
| <u>Master Pack Qty</u> | <u>UPC</u>          | <u>UPS</u>           |                      |
| 1.0000                 | 783209583153        | Yes                  |                      |

**Finish:**

Satin Nickel SN

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Dry Location  
Location

**Additional:**

MB Incandescent (Not Included)