



8592-71: One Light Outdoor Wall Lantern



Dimensions:

Width: 4 1/4" **Extends:** 5 1/2"
Height: 8 1/4" **Wire:** 6 1/2"
Mounting Proc.: Cap Nuts
Connection: Mounted To Box
Bulb Appearance: Clear

Bulbs:

1 - Medium A19 100w Max. 120v - Not included
 1 - LED Medium A19 8w Max. 120v - Not included
 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Collection: New Castle

Simple Details Create Stylish Outdoor Wall Lantern. Antique Bronze Solid Brass and Clear Glass.

Simple details create a stylish outdoor wall lantern. Antique Bronze solid Brass and clear glass.

UPC #:785652085925

Finish: Antique Bronze (71)

Material List:

1 Body - Brass - Antique Bronze
 1 Canopy - Brass - Antique Bronze

Safety Listing:

Safety Listed for Wet Locations
 Safety Listed for Wet Locations

Instruction Sheets:

English (HC-231)
 French (F-009)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear	4									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			2 1/16	4 1/2	2 3/4	5 1/2

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8592-71	1	785652085925	6.75	5.75	9	0.202	1.75	100	Yes

Master Pack		6	10785652085922	18	14.5	9.75	1.473	11.7	100	Yes
NJ Pallet		378		48	40	72	80	737.1		No
NV Pallet		378		48	40	73	81.111	737.1		No