

DS710-10Z



UPC Code: 07847769237

Country Of Origin: China

DS710-10Z

Brand Features

Leviton Decora Rocker-Slide Advance Mark 7® and Quicktronic® Helios Fluorescent Ballast Dimmers provide smooth, slide-action, full-range dimming for Fluorescent loads. They combine a Decora rocker switch with a contemporary full-range slender slide bar for precise lighting control. With a new, streamlined style, Decora dimmers and fan speed control complement any interior design and are compatible with other Decora devices.

Item Description

Decora Rocker-Slide 1200VA-120VAC, 1500VA-277VAC Fluorescent ballast and LED power supply dimmer for 0-10V, 60Hz, Single Pole or 3-Way, Class 2 Wiring Device - White, Ivory & Light Almond

Technical Information

Product Features

Action: Rocker Switch for ON/OFF, slide bar for lighting level control

Warranty: 5-Year Limited

Preset: Slide bar preserves desired lighting level

Color: White, Ivory, Light Almond

Switch Type: Single-Pole & 3-Way

Load Type: Electronic 0-10VDC Fluorescent

Available Colors: Ivory-I Wht-W Gry-G Blk-E Brwn-B Light Almond-T, R-Red

Wallplate: Order Separately

Type: Electro-Mechanical

Load Rating: 1200VA-120VAC, 1500VA-277VAC

Style Name: Decora

Ordering Notes: Included White, Ivory and Light Almond Color Kit

Standards and Certifications: cCSAus, NOM

Protection: Radio/TV Filter

Features and Benefits

- New aesthetically pleasing design with rocker switch and slender dimmer control slide bar
- Integrated linear full-range slide control for easy, precise operation
- Single pole or 3-way operation (when using 3-way switch); packaged with White, Ivory, and Light Almond color change kits
- Additional color change kits available in Black, Brown, Red and Gray
- Slim, compact housing fits easily into a standard wallbox and is suitable for multi-gang installations with other Decora products
- The slide bar location preserves the selected brightness level when the dimmer is switched OFF
- No fins for multi-gang installation
- Wired using leads, a Neutral wire is not required for operation
- Built-in radio/TV interference filter

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

