



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker

QBGFEP2015

UPC: 786679473474

Dimensions: 5.7 IN * 4.5 IN * 3 IN (L * W * H)

Notes: HACR rated

Warranty: 1 year

Specifications:

- **Special Features:** 30 mA Trip Sensitivity
- **Type:** Quicklag
- **Mounting:** Bolt-on
- **Circuit Breaker Type:** QBGFEP
- **Trip Type:** Non-Interchangeable
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V

Supporting documents:

- [Eatons Volume 4-Circuit Protection Catalog](#)
- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers Specification](#)

Certifications:

- UL 943

Product compliance: No Data

