



Search > Results for 45079 > CFL23/50/T2 45079 23W T2 SPIRAL 5000K MED PROLUME



CFL23/50/T2 45079 23W T2 SPIRAL 5000K MED PROLUME

Product Number: 45079
UPC: 807154450794

[Log In for Price and Availability](#)

Note: this product is only sold in multiples of 10 items

Specifications	Resources	Technical
Applications	Table lamps; Down lighting; Ceiling fixtures; Wall sconces; Vanity	
Average Life (Hrs)	8,000	
Base	Medium	
Brand	ProLume	
Bulb	T2	
CRI	82	
Color Temperature	5000	
Cross Reference - Osram Sylvania	CFL23EL/MINI/850	
Dimensional Dwg		
Dimmable	No	
ENERGY STAR	No	
Equivalent Wattage	100	
HTS code	8539310060	
Initial Lumens	1380	
Inner Carton Quantity	10	
Input Frequency (Hz)	60	
Markets	Residential, Commercial	
Master Carton Quantity	50	
Maximum Overall Diameter	2.13	
Maximum Overall Length	4.92	
Nominal Length	4.92	
Operating Position	Universal	
Prod Code	CFL23/50/T2	
Product Category	CFL Self-Ballasted	
Product Description	23W T2 SPIRAL 5000K MED PROLUME	
Product Number	45079	
Start Type	Instant Start	
Voltage (V)	120	
Warranty (Yrs)	2	
Wattage (W)	23	

Substitute Items:



A19FR9/827/ECO/LED 80973 A19 9.5W 2700K NON-DIMMABLE 240 DEGRE



Products

Lamps



Ballasts



Luminaires



Resources

- Catalogs
- Sell Sheets
- New Products

Contact Us

Corporate Office:
Halco Lighting Technologi
2940 Pacific Drive
Norcross, GA 30071
Toll Free: 800.677.3334
Office: 770.242.3612
Fax: 800.880.0822
Email: customer@halco.com



Copyright © 2017 - Halco Lighting Technologies

- [Home](#)
- [News](#)
- [About Us](#)
- [FAQ](#)
- [Site Map](#)
- [Privacy P](#)