



Item #: **F833-SL**  
 Product Family Name: **Kewl**  
 Category: **Interior Fan**  
 Certification: **4000048**  
 Patents: U.S. Patent(s): D715,418; D726,299  
 Notes:

UPC Code: **706411044311**  
 Finish: **Silver**  
 Category Type: **Ceiling Fan**

Image File Name:  
 F833-SL\_0.jpg



## MEASUREMENTS

Blade Finish:	Reversible Blades:		
	<b>No</b>		
Blade Material:	Slope:		
<b>ABS Construction</b>	<b>No</b>		
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
<b>52</b>	<b>3</b>	<b>20</b>	<b>12.17</b>
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
<b>3.5</b>	<b>.75</b>	<b>6</b>	<b>.75</b>
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
<b>11.00</b>	<b>8.75</b>	<b>80</b>	<b>153x15mm</b>

	Low:	Low/Med:	Medium:	Med/High:	High:
<b>RPM:</b>	104		145		201
<b>Amps:</b>	0.27		0.34		0.46
<b>Watts:</b>	17.900		30.100		55.000
<b>CFM:</b>	3460.00		4561.00		6304.00
<b>CFM/Watts</b>	193.30		151.53		114.62



## FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
<b>No</b>	<b>Yes</b>	<b>Yes</b>
	Included Remote Control:	Included Wall Control:
		<b>WC105-WH</b>
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	<b>RCS223</b>	<b>WCS223</b>

## LAMPING

No. of Bulbs:	Light Type:			
	<b>N/A</b>			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
<b>No</b>	<b>No</b>			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
<b>No</b>				

## GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



## SHIPPING

Carton Width:	Carton Height:	Carton Length:	
<b>10.130</b>	<b>9.630</b>	<b>24.750</b>	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
<b>14.762</b>	<b>1.397</b>	<b>Yes</b>	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
			<b>1</b>



ENERGY  
 STAR  
 Yes



Title 17  
 Yes



ETL Intertek  
 Yes