

# Color-Keyed®

**Splice Connector**  
**T&B Catalog Number:**



54806  
 78621054806  
 Active

**UPC Number:**  
**Status:**  
**Description:**

Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #4 AWG, Length 1.75 Inches, Diameter 0.39 Inches, Tin Plated, Die Code 29, Die Color Code Gray

**Features**

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.



**General**

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#4 AWG
Wire Size Flex	91/24 = 36.7 kcmil
Die Color	Gray
Die Code	29

**Dimension Information**

A (inches)	1.75
E (inches)	0.39

**Specifications**

Voltage Rating	600V
----------------	------

**Packaging**

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	3 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
 Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com