

# iTOOLco.

## REAL TENDER™

### Easier

- Easy to set up and transport
- Light and maneuverable
- Easy one person operation
- Horizontal or vertical use

### Faster

- Saves time
- Crank handle for faster re-spooling

### Safer

- Prevents injuries from lifting and handling rope
- No more lifting heavy wire spools

### Smarter

- Axle-less technology
- Multi-directional
- Rolls over rough terrain on job site
- Cleaner handling of expensive rope (high & dry)

### Specifications

- Handle length: 49"
- Width: 23"
- Weight: 38 lb.
- Spool widths: 12"-35"
- Spool diameters: 12"-32"
- 300 lb. Weight limit

### NOTE: Patented

Model	Description
<b>RT01</b>	Real Tender



**WORKS WITH  
ANY MFR'S SPOOL**



*Conveniently store  
and move Real Jacks  
on the Real Tender.*

**6**  
**YEAR**  
LIMITED  
WARRANTY

MADE IN THE  
**USA**  
WITH GLOBAL  
COMPONENTS

**GREAT FOR  
MC CABLE**



## REAL SPOOL™

- Holds up to 300 lb.
- Will not splinter like a wood spool
- Weighs less than a wooden spool
- Wood splinters cannot fray or damage the rope
- Made out of heavy US steel, making it more durable than the average spool
- Works great for iTOOLco's Pull-Slick

Model	Description
<b>RS01</b>	Real Spool



**iTOOLco.**

**865-670-3713 • iTOOLco.com**

Innovative Tools For Professional Electricians & Contractors

150818\_FL\_iTOOLco8