



List Price \$3,041.00 USD

Availability **Stock Item:** This item is normally stocked in our distribution facility.

### Technical Characteristics

Approvals	UL Listed - CSA Certified - IEC Rated
Circuit Breaker Type	Standard Interrupting
For Use With	I-Line Panels and Switchboards
Marketing Trade Name	Square D
AC Magnetic Trip Setting	1250A - 2500A Adjustable Trip
Ampere Rating	250A
Frame Type	K-Frame
HACR Rated	Yes
Voltage Rating	600VAC
Mounting Type	Plug-On
Weight	7 Pounds
Number of Poles	3-Pole
Short Circuit Current Rating	25kA@480VAC
Phase Connection	ABC
Space Required	3
Type	KA
Wire Size	(1)#4 to 350 AWG/kcmil(Al/Cu)
Width	4.50 Inches
Depth	4.75 Inches
Height	8.00 Inches

### Shipping and Ordering

Category	01025 - Circuit Breakers, Thermal Magnetic, 600 Vac, Type KA & KH, UL, I-Line
Discount Schedule	DE2
Article Number	785901031673
Package Quantity	1
Weight	8.67 lbs.
Availability Code	S
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.