



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH324FGK

UPC: 782113206660

Dimensions: 30 IN * 18 IN * 9.5 IN (L * W * H)

Notes: Suitable for service entrance use with a Neutral Kit installed

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 200A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 15 at 240 Vac Std. 1 Ph, 25 at 240 Vac Std. 3 Ph, 15 at 240 Vac TD 1 Ph, 60 at 240 Vac TD 3 Ph, 40 at 250 Vdc

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Drawing Dataset](#)
- [Eaton Specification Sheet - DH324FGK](#)

Certifications: No Data

Product compliance: No Data

