

Product availability : Stock - Normally stocked in distribution facility



Price\* : 5705.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact J
Trip unit technology	Thermal-magnetic
Breaking capacity code	J

### Complementary

Line Rated Current	175 A
Number of poles	3
Number of Poles	3P
Breaking capacity	20 kA 250 V DC 100 kA 240 V AC 65 kA 480 V AC 25 kA 600 V AC
System Voltage	250 V DC 600 V AC
[Ics] rated service short-circuit breaking capacity	80 %
Mounting Type	I-Line
Electrical connection	I-Line connection line Lugs load
Wire Size	AWG 4...AWG 4/0 (aluminium/copper)
Phase connection	ABC
Magnetic hold current	875 A
Magnetic tripping current	1750 A

### Environment

Product certifications	IEC UL listed CSA
------------------------	-------------------------

CCC  
CE

---

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

---

### Ordering and shipping details

---

Category	01117 - HG, HJ, JG, JJ I-LINE BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901700715
Nbr. of units in pkg.	1
Package weight(Lbs)	6.759999999999998
Returnability	Y
Country of origin	MX

---

### Offer Sustainability

---

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---