



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Heavy Duty Safety Switch

DH324NRK

UPC: 782113206691

**Dimensions:** 10 IN \* 15.52 IN \* 28.12 IN (L \* W \* H)

**Notes:** No Data

**Warranty:** Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 200A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 15 at 240 Vac Std. 1 Ph, 25 at 240 Vac Std. 3 Ph, 15 at 240 Vac TD 1 Ph, 60 at 240 Vac TD 3 Ph, 40 at 250 Vdc

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH324NRK](#)

**Certifications:** No Data

**Product compliance:** No Data

