



Hoffman

Continuous Hinge, Type 4X

Catalog Number: A14128CHQRFGW
US List Price (USD): \$232.90

Bulletin Number:

- A48

Material:

- Fiberglass



Model Code:

- 31290

Ship Wt. Std. Pkg. (lbs):

- 8.5

Interchangeable:

- False

IP Rating:

- IP66

Industry Standards:

Mounting brackets required to meet UL/CSA external mounting requirements. UL 508A Listed; Type 4, 4X, 12, 13; File No. E61997 cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12, 13; File No. E61997 Enclosure flammability evaluated per UL 508A Window flammability evaluated per UL 508A NEMA/EEMAC Type 4, 4X, 12, 13 CSA File No. 42186: Type 4, 4X, 12, 13 IEC 60529, IP66

Description

The efficient design and simple construction of these enclosures make them durable in corrosive environments, yet aesthetically pleasing. Corner latches provide unobstructed access. The continuous hinge provides a secure seal, and double latching creates added security.

Applications:

The efficient design and simple construction of these enclosures make them durable in corrosive environments, yet aesthetically pleasing. Corner latches provide unobstructed access. The continuous hinge provides a secure seal, and double latching creates added security.

Specifications:

- Compression-molded fiberglass has outstanding chemical- and temperature-resistance qualities and exhibits excellent weatherability and physical properties
- Fiberglass is easily punched, drilled, filed or sawed
- Gasket assures water-tight and dust-tight seal
- Polyester mounting brackets and stainless steel attachment screws are provided with each enclosure
- Scratch-resistant polycarbonate windows are permanently bonded in place
- Molded-in-place threaded brass inserts and plated steel screws are provided for mounting optional panels and terminal block kits
- Removable hinged cover attached to body with Type 316 stainless steel hinge pin
- Screw-cover enclosures are secured with two captivated Type 316 stainless steel slotted cover screws
- Enclosures with quick-release latches have corrosion-resistant polyester latches located in corners that provide unobstructed access to enclosure
- Hinge pin and bail are corrosion-resistant Type 316 stainless steel
- Padlock provisions included
- Material is halogen free

Finish:

Standard fiberglass material finish is light-gray inside and out. Optional steel panels are painted white. Optional stainless steel, aluminum, conductive and composite panels are unpainted.

Accessories:

- H2OMIT Vent Drains, Type 4X
- HOL-SEALERS Non-Metallic Hole Seals
- Panels for Junction Boxes
- Threaded Panel Extenders
- Quick-Release Latch Kit
- Swing-Out Panel Kit

Modifications and Customizations:

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

Notes:

Purchase panels separately. Optional stainless steel, aluminum, conductive and composite material panels available for most sizes.

Technical Data

Continuous Hinge, Type 4X

Catalog Number	A14128CHQRFGW
A in.	14
B in.	12
C in.	8
K in.	1.81
F in.	7.45
Panel Size D x E in.	12.75 x 10.88
J in.	6.50
M in.	12.25
N in.	10.25
T in.	0.15
Type	Window Cover, Quick Release
Q in.	13.59
P in.	12.25
Overall L x W in.	14.55 x 12.55
Steel Panel	A14P12
Mounting G x H in.	14.94 x 10.00
U in.	11.59
O in.	10.25
Alum. Panel	A14P12AL

Certifications



EU Certification



UL Certification

Documents



Instruction Manual



2D DXF CAD



DOC






3D STEP CAD



Spec Sheet

Accessories

Item		
	HOL-SEALERS Non-Metallic Hole Seals	ASPB05075NM
	Panels for Junction Boxes	A14P12AL
	Panels for Junction Boxes	A14P12