


Relay Sockets




Description	Poles & Throws	Ratings	Terminal Type	Part Number	Fig. No.
8 Pin Midget Socket, DIN Rail Mountable	DPDT	300 V, 10 Amps	Pressure Clamp Screws	SR7008A	1
8 Pin Octal Socket, DIN Rail Mountable	DPDT	300 V, 10 Amps	Pressure Clamp Screws	SR67083A	2
11 Pin Octal Socket, DIN Rail Mountable	3PDT	300 V, 10 Amps	Pressure Clamp Screws	SR67113A	3
11 Pin Square Base Socket, DIN Rail Mountable	3PDT	300 V, 10 Amps	Binder Head Screws	SR6811N	4
14 Pin Miniature Socket, DIN Rail Mountable	4PDT	300 V, 7 Amps	Pressure Clamp Screws	SR6914A	5
14 Pin Miniature Socket, DIN Rail Mountable	4PDT	240 V, 10 Amps	Pressure Clamp Screws	SR7014A	6
8 Pin Miniature Socket, DIN Rail Mountable	DPDT	300 V, 7 Amps	Pressure Clamp Screws	SR6908A	1
DIN rail, 1 Metre Length, Aluminum	--	--	--	SR-100N	--



*"It's better to act too quickly
than it is to wait too long."*

— Jack Welch

General Purpose



Contact Rating	Poles & Throws	Coil Volts	Terminal Type	Mounting Method	Avail. Socket	Indicator Light	Pin Number	Part Number	Fig. No.
3 A	DPDT	5 DC	PCB	---	---	No	8	SR15P207D1	1
3 A	4PDT	24 DC	Plug-in	Socket	SR6914A	No	14	SR69S400D4	2
3 A	4PDT	110/120AC	Plug-in	Socket	SR6914A	No	14	SR69S400A7	2
5 A	DPDT	12 DC	Plug-in	Socket	SR6908A	No	8	SR69S200D3	3
5 A	DPDT	24 DC	Plug-in	Socket	SR6908A	No	8	SR69S200D4	3
5 A	4PDT	12 DC	Plug-in	Socket	SR6914A	No	14	SR69S400D3	3
10 A	SPDT	120 AC	.250" QC	Flange	---	No	5	SR61F1-A120	4
10 A	DPDT	12 AC	Octal	Socket	SR67083A	No	8	SR67S200A3	5
10 A	DPDT	12 DC	Plug-in	Socket	SR7008A	No	8	SR70S200D3	6
10 A	DPDT	12 DC	Octal	Socket	SR67083A	No	8	SR67S200D3	6
10 A	DPDT	12 DC	Octal	Socket	SR67083A	Yes	8	SR67S215D3	5
10 A	DPDT	24 AC	Plug-in	Socket	SR7008A	No	8	SR70S200A4	6
10 A	DPDT	24 AC	Octal	Socket	SR67083A	No	8	SR67S200A4	5
10 A	DPDT	24 AC	Octal	Socket	SR67083A	Yes	8	SR67S215A4	5
10 A	DPDT	24 DC	Plug-in	Socket	SR7008A	No	8	SR70S200D4	6
10 A	DPDT	24 DC	Octal	Socket	SR67083A	No	8	SR67S200D4	5
10 A	DPDT	24 DC	Octal	Socket	SR67083A	Yes	8	SR67S215D4	5
10 A	DPDT	120 AC	Plug-in	Socket	SR7008A	No	8	SR70S200A7	6
10 A	DPDT	120 AC	Octal	Socket	SR67083A	No	8	SR67S200A7	5
10 A	DPDT	120 AC	Octal	Socket	SR67083A	Yes	8	SR67S215A7	5
10 A	DPDT	240 AC	Plug-in	Socket	SR7008A	No	8	SR70S200A9	6
10 A	DPDT	240 AC	Octal	Socket	SR67083A	No	8	SR67S200A9	5
10 A	3PDT	24 AC	Octal	Socket	SR67113A	No	11	SR67S300A4	5
10 A	3PDT	24 AC	Octal	Socket	SR67113A	Yes	11	SR67S315A4	5
10 A	3PDT	24 DC	Octal	Socket	SR67113A	Yes	11	SR67S315D4	5
10 A	3PDT	120 AC	Octal	Socket	SR67113A	No	11	SR67S300A7	5
10 A	3PDT	120 AC	Octal	Socket	SR67113A	Yes	11	SR67S315A7	5
10 A	4PDT	120 AC	Plug-in	Socket	SR7014A	No	14	SR70S400A7	7
13 A	DPDT	24 AC	Plug-in	Socket	SR6811N	No	8	SR68S200A4	8
13 A	DPDT	120 AC	Plug-in	Socket	SR6811N	No	8	SR68S200A7	8
13 A	3PDT	24 AC	Plug-in	Socket	SR6811N	No	11	SR68S300A4	8
13 A	3PDT	120 AC	Plug-in	Socket	SR6811N	No	11	SR68S300A7	8
13 A	3PDT	120 AC	Plug-in	Socket	SR6811N	Yes	11	SR68S315A7	8
13 A	3PDT	240 AC	Plug-in	Socket	SR6811N	No	11	SR68S300A9	8

NOTE: Contact factory for mounting hole dimensions.