

# Standard Size



	White	Brown	Ivory	Almond	Gray	Red	Box Quantity	Carton Quantity	Weight per 100 units
 <b>1 Blank (Box Mounting 3.281") (1B)</b>	90151	91151	92151	77151A	77151G	77151R	25	250	6 lbs.
 <b>2 Blanks (Box Mounting 3.281") (2B)</b>	90152	91152	92152	77152A	77152G	77152R	10	100	11 lbs.
 <b>3 Blanks (Box Mounting 3.281") (3B)</b>	90153	91153	92153	77153A			10	80	16 lbs.
 <b>One 20A TL Receptacle (1.620" ID Hole) (3R)</b>	90111	91111	92111		77111G	77111R	25	250	5 lbs.
 <b>One 30A 3 &amp; 4 Wire TL Receptacle 1.730 ID Hole (3330R)</b>	90229	91229	92229		77229G		25	250	5 lbs.
 <b>30/50A 3 Wire Range/Dryer Receptacle 2.125" ID Hole (3D)</b>	90221	91221	92221	77221A	77221G	77221R	25	250	5 lbs.
 <b>30/50A 3 Wire Range/Dryer Receptacle 2.125" ID Hole (N23D)</b>	90227	91227	92227	77227A	77227G		10	100	10 lbs.
 <b>30/50/60A 3 &amp; 4 Wire Receptacles 2.480" ID Hole (5R)</b>	90223	91223	92223		77223G		10	100	10 lbs.
 <b>30/50/60A 3 Wire Receptacles 2.625" ID Hole (L5R)</b>	90225	91225	92225				10	100	10 lbs.
 <b>30/50/60A 4 Wire Receptacles 2.255" ID Hole (P5R)</b>	90228	91228	92228				10	100	10 lbs.
 <b>Block Duplex/GFI Receptacle (SRM)</b>	90401	91401	92401	77401A	77401G	77401R	25	250	5 lbs.
 <b>2 Block Duplex/GFI Receptacles (2SRM)</b>	90402	91402	92402	77402A	77402G	77402R	10	100	9 lbs.