₩elbourne CFL

HEXAGONAL FRAME WORK WITH VINE INSPIRED SCROLLS. ETCHED FLAT GLASS PANELS. ENERGY EFFICIENT. CAST ALUMINUM CONSTRUCTION WITH POWDER COAT FINISH.







P5682-31EB



P5682-20EB



P5684-31EB

P5482-20EB Antique Bronze P5482-31EB Textured Black One-light post lantern. Size: 9-1/2" dia., 21-1/4" ht. Fits 3" post (order separately). Lamp: One GU24 CFL lamp, 18w max.

P5582-20EB Antique Bronze P5582-31EB Textured Black One-light hanging lantern. Size: 9-1/2" dia., 15" ht., Overall ht. w/ chain 51"; wire 10'. Lamp: One GU24 CFL lamp, 18w max.

P5682-20EB Antique Bronze P5682-31EB Textured Black One-light wall lantern. Size: 6-1/2" W., 13-1/4" ht. Extends 9". H/CTR 3-1/2". Lamp: One GU24 CFL lamp, 18w max.



P5683-20EB Antique Bronze P5683-31EB Textured Black One-light wall lantern. Size: 9-1/2" W., 18" ht. Extends 9-3/4" H/CTR 8-1/2". Lamp: One GU24 CFL lamp, 18w max.



P5684-20EB Antique Bronze P5684-31EB Textured Black One-light wall lantern. Use with or without tail. Size: 9-1/2" W., 31-1/4" ht. with tail. 23-1/4" ht. without tail. Extends 10-1/2". H/CTR 19" Lamp: One GU24 CFL lamp, 26w max.





See page 285 for additional chain, and page 589 for posts.

₩elbourne

HEXAGONAL FRAMEWORK WITH VINE-INSPIRED SCROLLS.BEVELED CLEAR GLASS PANELS IN FLAT ETCHED GLASS IN ANTIQUE BRONZE





P5582-20 Antique Bronze P5582-30 Textured White P5582-31 Textured Black One-light hanging lantern. Size: 9-1/2" dia., 15" ht., Overall ht. w/ chain 51"; wire 10' Lamp: One medium base lamp, 100w max.

P5681-20 Antique Bronze P5681-30 Textured White P5681-31 Textured Black One-light wall lantern. Size: 6-1/2" W., 16-7/8" ht. Extends 9-1/4". H/CTR 13-1/4". Lamp: One medium base lamp, 100w max.

P5682-20 Antique Bronze P5682-30 Textured White P5682-31 Textured Black One-light wall lantern. Size: 6-1/2" W., 13-1/4" ht. Extends 9". H/CTR 3-1/2". Lamp: One medium base lamp, 100w max.



P5482-20 Antique Bronze P5482-30 Textured White P5482-31 Textured Black One-light post lantern. Size: 9-1/2" dia., 21-1/4" ht. Fits 3" post (order separately). Lamps: One medium base lamp, 100w max.

See page 285 for additional chain, and page 589 for posts.

P5483-20 Antique Bronze P5483-30 Textured White P5483-31 Textured Black Three-light post lantern. Size: 13" dia., 26" ht. Fits 3" post (order separately). Lamps: Three candelabra base lamps, 60w max. P5683-20 Antique Bronze P5683-30 Textured White P5683-31 Textured Black One-light wall lantern. Size: 9-1/2" W., 18" ht. Extends 9-3/4" H/CTR 8-1/2". Lamp: One medium base lamp, 100w max.

| Welbourne

BE BOLD WITH NATURAL UNDERTONES AND GEOMETRIC FORMS. HEXAGONAL CAST ALUMINUM FRAMEWORK WITH VINE-INSPIRED SCROLLS. BEVELED CLEAR GLASS PANELS IN TEXTURED BLACK FINISH. FLAT ETCHED GLASS IN ANTIQUE BRONZE FINISH.









P5485-31EB Textured Black One-light post lantern. White glass chimney. Size: 13" dia., 26" ht. Fits 3" post (order separately). Ballast: 120V/277V HPF

Lamp: One 26w, 32w or 42w 4-pin Quad CFL. GX24q-3/-4 base.

P5486-31 Textured Black One-light post lantern. 120V NPF magnetic ballast. White glass chimney. Size: 13" dia., 26" ht. Fits 3" post (order separately). Lamp: One 100w high pressure sodium E17. P5684-20 Antique Bronze P5684-31 Textured Black One-light wall lantern. Use with or without tail. Size: 9-1/2" W., 31-1/4" ht. with tail. 23-1/4" ht. without tail. Extends 10-1/2". H/CTR 19" Lamp: One medium base lamp, 100w max. P5690-20 Antique Bronze P5690-31 Textured Black Three-light wall lantern. Size: 13" W., 22-1/4" ht. Extends 14". H/CTR 8-1/2". Lamps: Three candelabra base lamps, each 60w max.

