



Ordering Information

Catalog No.	Rating	Finish	Mounting	Compatible Connector Kits
PLD120BK	120W, 1.0A	Black	Snaps in directly to any compatible PowerTrip Connector Kit	9099WH, BK 9033WH, BK 6099WH, BK 6033WH, BK 6199WH, BK 6133WH, BK
PLD120WH	120W, 1.0A	White		
PLD240BK	240W, 2.0A	Black		
PLD240WH	240W, 2.0A	White		
PLD300BK	300W, 2.5A	Black		
PLD300WH	300W, 2.5A	White		
PLD360BK	360W, 3.0A	Black		
PLD360WH	360W, 3.0A	White		
PLD480BK	480W, 4.0A	Black		
PLD480WH	480W, 4.0A	White		
PLD600BK	600W, 5.0A	Black		
PLD600WH	600W, 5.0A	White		
PLD720BK	720W, 6.0A	Black		
PLD720WH	720W, 6.0A	White		
PLD840BK	840W, 7.0A	Black		
PLD840WH	840W, 7.0A	White		
PLD900BK	900W, 7.5A	Black		
PLD900WH	900W, 7.5A	White		
PLD960BK	960W, 8.0A	Black		
PLD960WH	960W, 8.0A	White		
PLD1320BK	1320W, 11.0A	Black		
PLD1320WH	1320W, 11.0A	White		
PLD1440BK	1440W, 12.0A	Black		
PLD1440WH	1440W, 12.0A	White		

Features

- Wire Terminals:** #8 screws for 12 or 14 ga. solid copper wires.
- Reset Rocker:** Easy switch like breaker re-set actuator with ON/OFF markings. Red color indicates OFF position. Can be used as standard ON/OFF switch
- Panel Mount:** Breaker snaps into PowerTrip track connector without the use of tools.

Electrical

Capacity is 120 volts, 60Hz. All Lytespan Track luminaires are polarized and continuously grounded throughout. Electrical conductors are concealed in an insulating liner. Intended for wiring to branch circuit building wire with ground. All wiring must be in accordance with National and Local Codes.

Short Circuit Current Rating (AIC): 1kA

Use 90° C minimum supply wire.

Labels

cULus listed.

Job Information

Type:

Job Name:

Cat. No.:

Lamp(s):

Notes: