JUNO®

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

PRODUCT DESCRIPTION

IC Air-Loc® Housing • Energy efficient, sealed housing • Can be completely covered with insulation • When used with Air-Loc Gasket (see accessories), stops infiltration and exfiltration of air, reducing heating and cooling costs • Trims shown with Air-Loc symbol **AIR-LOC** do not require a gasket.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected–see reverse.

Socket Medium base porcelain with nickel-plated copper screw shell • Adjustable socket plate and detachable socket with snap-in springs to accommodate various lamp and trim combinations • Socket plate secured at two points for consistent, straight lamp positioning.

Trims Trim selection shown on reverse.

Labels U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps • UL Listed/CSA certified • Trim 239, 241 and 242 are wet location approved for covered ceiling applications • Trims 28, 29 are wet location approved for covered ceilings, **must be used with outdoor rated lamps**.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

INSTALLATION

Real Nail 3 Bar Hangers Telescoping, Patented (US Patent D552,969) Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot (location identified on the mounting frame) and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.

Junction Box Pre-wired junction box provided with (5) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90˚ C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots • Supplied with **push-in electrical connectors** for fast installation.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation • Sight lines embossed on mounting frame to allow for easy viewing when aligning fixtures.

Housing IC housing, .032" aluminum sealed for Air-Loc Compliance • Housing is vertically adjustable to accommodate up to a 1" ceiling thickness.

DIMENSIONS

7 1/8"

7 1/2"

13 1/2"
Will expand to 25"
(Reduces to 8 1/2" with breakaway feature)

9 1/2"

13 1/8"

6 7/8" CEILING CUTOUT

ACCESSORIES

Catalog No.	Description
ALG6	Air-Loc Gasket

To order, specify catalog number.

PRODUCT CODES

Catalog Number	Input Voltage	Lamp Rating (max.)
IC22W	120V	A19/BR30/BR40/PAR16/PAR20/PAR30/PAR30L/PAR38/R20 (See reverse for max. trim rating)

REV-5/15

6" ECONOMY UNIVERSAL IC HOUSING

INCANDESCENT LAMPS

IC22W

TRIMS/LAMPS

Cat. No.	Description	Max. Lamp Rating		Cat. No.	Description	Max. Lamp Rating
24B-WH	Conical Black Baffle	50W PAR30, 75W PAR30L, 65W BR30		248W-WH	R20 Eyeball in White Baffle	50W PAR20/R20
24B-SC	Conical Black Baffle					
24B-ABZ	Conical Black Baffle			249B-WH	BR30 Eyeball in Black Baffle	75W PAR30L, 65W BR30
24B-BL	Conical Black Baffle			249W-WH	BR30 Eyeball in White Baffle	
24W-WH	Conical White Baffle					
25B-WH	Straight Black Baffle	50W PAR30, 65W BR30		264B-WH	PAR30 Adjustable - Black Baffle	50W PAR30
25B-SC	Straight Black Baffle			264W-WH	PAR30 Adjustable - White Baffle	
25B-ABZ	Straight Black Baffle					
25B-BL	Straight Black Baffle			267C-WH	PAR30 Adjustable - Clear Alzak®	50W PAR30
25W-WH	Straight White Baffle			267G-WH	PAR30 Adjustable - Gold Alzak®	
28B-WH	Conical Black Baffle	60W A19, 65W BR30, † 75W PAR30/30L, 90W PAR38, 90W BR40		267B-WH	PAR30 Adjustable - Black Alzak®	
28W-WH	Conical White Baffle			267HZ-WH	PAR30 Adjustable - Haze	
				267WHZ-WH	PAR30 Adjustable - Wheat Haze	
29C-WH	Deep Cone Clear Cone	60W A19, 65W BR30, † 75W PAR30/30L, 90W PAR38, 90W BR40		XR30101WH	AVIO Square Gimbal Ring - White	75W PAR30
29W-WH	Deep Cone White Cone			XR30101BL	AVIO Square Gimbal Ring - Black	
				XR30101GP	AVIO Square Gimbal Ring - Graphite	
27C-WH	Conical Cone in Clear Alzak®	50W PAR30, 75W PAR30L, 65W BR30		XR30101SL	AVIO Square Gimbal Ring - Silver	
27G-WH	Conical Cone in Gold Alzak®			239-WH ◆	Frosted Lens	40W A19
27B-WH	Conical Cone in Black Alzak®					
27PT-SC	Conical Cone in Pewter Alzak®			241-WH ◆	Drop Opal with Reflector	40W A19
27W-WH	Conical Cone in Gloss White			241-PW ◆	Shower/Closet Light	
27HZ-WH	Conical Cone in Haze					
27WHZ-WH	Conical Cone in Wheat Haze			242-WH ◆	Shower Trim,	45W PAR38
27WHZ-ABZ	Conical Cone in Wheat Haze			242-SC ◆	Frosted Lens with Clear Center	
244B-WH	Conical Black Baffle	75W PAR30L, 60W PAR30, 65W BR30		242-ABZ ◆		
244W-WH	Conical White Baffle			9324-SC	Luminous Disc	50W PAR30, 65W BR30, 75W PAR30
247C-WH	Cone - Clear Alzak®	75W PAR30L, 65W BR30, 75W PAR30		9702	Luminous Collar	50W PAR30, 65W BR30, 75W PAR30L
247G-WH	Cone - Gold Alzak®					
247B-WH	Cone - Black Alzak®			9024W-WH	White Octagonal w/White Baffle	50W PAR30, 65W BR30, 75W PAR30
247HZ-WH	Cone - Haze					
247WHZ-WH	Cone - Wheat Haze			9524-SC	Chrome Band	65W BR30, 50W PAR30, 75W PAR30L
250-WH	Open Frame	65W BR30				
250-SC	Open Frame					
250-ABZ	Open Frame					
252-WH	Regressed Open Frame	75W R/BR30				
231C-WH	Multiplier - Clear Alzak®	60W A19				
231G-WH	Multiplier - Gold Alzak®					
231W-WH	Multiplier - Gloss White					
226B-WH	Black Cylinder w/Black Baffle	60W PAR16				
226W-WH	White Cylinder w/White Baffle					
228-WH	R20 Regressed Eyeball	50W PAR20/R20				
229-WH	BR30 Regressed Eyeball	75W PAR30L, 65W BR30				
229-SC	BR30 Regressed Eyeball					
229-ABZ	BR30 Regressed Eyeball					
229-BL	BR30 Regressed Eyeball					

Trim Size: 7⅝" O.D. (except Cat. Nos. 228, 229, 241, 9024, - 8" O.D., Cat. No. 9702 - 7¾" O.D.).
Trim Finish: ABZ - Classic Aged Bronze, BL - Black, GP - Graphite, PW - Plastic White (Polycarbonate material shower trim), SC - Satin Chrome, SL - Silver, WH - White.
Alzak is a registered trademark of Alcoa Corp.
Note: In Canada when insulation is present, Type IC fixtures must be used.

AIR-LOC JUNO IC housings meet IECC Energy Code requirements per ASTM E283. Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housings.

◆ UL Listed for use in wet location.

† Suitable for wet locations, ceiling mount only when used with 75W PAR30 or 90W PAR38 OUTDOOR RATED LAMPS.

** NOTE: TR6 Trim Ring compatible with 24, 25, 27, 244, 247, 264, 267 trims.