



Outdoor Lighting

HUBBELL® ExpressLine



Hubbell Lighting ExpressLine & Lightscaper Families

2012



ExpressLine

by Hubbell Lighting

The name Hubbell has long been associated with quality products sold through the Electrical Distribution channel. Our Hubbell Lighting products are readily accepted by contractors and universally recognized as leading in quality and value by specifiers. Hubbell Lighting continues this tradition of quality, strengthening our support of this partnership today.

The *ExpressLine* program expands our stock product range, and simplifies our business practices. This new family contains over 100 stock and flow units,

including the ALL NEW Laredo LNC LED Wallpack for maximum energy savings. The *ExpressLine* program provides quick-turn

solutions to the lighting challenges brought to you each day. The merchandising cartons are designed to help you quickly select the right fixture for each task. *ExpressLine* is just one part of a complete lighting solution from Hubbell Lighting.



Lightscaper

by Hubbell Lighting



Adding elegance, value and security to your home or business. Go Green with Hubbell Lightscaper® LED products. Offering a long life, easy to install, no maintenance LED lighting system, Hubbell Lightscaper® LED fixtures feature popular styles to enhance any landscape while providing safety and security.



Each fixture is professional grade die-cast aluminum construction, built to perform. Path and flood fixtures come complete with stake, 4' of fixture cable and "Smart Connect" tool-free connector as well as a flat surface mount for decks or other applications. The 56 watt control center completes the system and features: UL listed non-metallic housing, grounded cord set, photocontrol and easy cable connect. Complete fixture information on each carton includes: features, lighting layouts and dimensions.



LED Facade Flood

Catalog # Description

Wt.



NEW ALF-6LU-5K-BZ 10.7w LED, 120/208/240/277V

4.0

Excellent for small floodlighting applications such as signs, façade, landscape accent or small area illumination. The compact size allows the flood to be easily hidden or blend into the landscape environment. This floodlight produces 489 lumens with 5000K CCT.



Facade Flood

Catalog # Description

Wt.



F-050H1 50w PS, 120V

8lbs

Designed for close setbacks from walls, signs, or small areas.

F-070H1 70w PS, 120/208/240/277V

9 lbs

Wide uniform beam covers area four times the

F-100H1 100w PS, 120/208/240/277V

10 lbs

setback distance. Cast aluminum housing, polycarbonate

F-070S1 70w HPS, 120V

7 lbs

door, tempered glass lens, tool-free entry, 1/2" cast

F-150S1 150w HPS, 120V

8 lbs

aluminum swivel knuckle, dark bronze finish.

F-042F8 42w CFL, 120-277V

5 lbs

For use in wet locations. Lamp included. 0.6 EPA.



Microliter® Floodlight

Catalog # Description

Wt.



MIC-0100H-358 100w PS, 120/208/240/277V

13 lbs

Medium beam flood for setbacks of six feet or more. Beam

MIC-0150P-358 150w PS, 120/208/240/277V

14 lbs

coverage is two times setback distance. Cast aluminum

MIC-0150S-258 150w HPS, 120/208/240/277V

14 lbs

housing and door. Twin-screw closure with HubbellGard™

MIC-0150S-651 150w HPS, 120V

10 lbs

treated hardware. Tempered glass lens, rotatable parabolic reflector system for best beam utilization. Large, 1/2" cast aluminum swivel knuckle, dark bronze textured finish. For use in wet locations. Lamp included. 0.7 EPA.



Miniliter® V Wide Flood

MHS-Y-250P8 250w PS, 120/208/240/277V

22 lbs

Compact, 400w size flood. Very wide beam with uniform

MHS-Y-320P8 320w PS, 120/208/240/277V

24 lbs

distribution. Beam coverage is four times setback distance.

MHS-Y-400P8 400w PS, 120/208/240/277V

26 lbs

Cast aluminum housing and door. Tool-free lens/door access.

MHS-Y-250S8 250w HPS, 120/208/240/277V

24 lbs

Tempered glass lens, steel mounting yoke, dark bronze

MHS-Y-400S8 400w HPS, 120/208/240/277V

28 lbs

textured finish. For use in wet locations.

Lamp included. 1.4 EPA.



Quartz Floodlights

Q-150-B 150w, 120V, bronze

1.4 lbs

A wide range of white light, instant-on floods. Soft, uniform

Q-150-W 150w, 120V, white

1.4 lbs

beam with coverage of two to three times setback distance.

Q-300-B 300w, 120V, bronze

2.4 lbs

Cast aluminum housing and door. Single screw or stainless

Q-300-W 300w, 120V, white

2.4 lbs

steel latch closure for weather-tight gasket seal. 1/2" cast

Q-500-B 500w, 120V, bronze

2.7 lbs

aluminum swivel knuckle mounting. Bronze or white powder

Q-500-W 500w, 120V, white

2.7 lbs

coat finish. For use in wet locations. Lamp included.



Q-300-W



Q-500-B



*Supplied with a 500 and 300w lamp for twice the life and brightness choice.

Quartz Worklights

Catalog #	Description	Wt.
QWL-150C	150w clamp mount	2 lbs
QWL-500S*	300/500w hand stand mounting	4 lbs
QWL-1000T	2x500w tripod 2 in 1	27 lbs



Versatile task lighting fixtures, five-foot cord set, weather-tight switch, 120V, protective guard, adjustable aiming. Lamps included. UL listed. QWL-1000T features adjustable tripod unit with handy removable top for maximum versatility. Twin 500w units with guards and individual switching. Tripod and fixtures are safety yellow finish with black accents.



Motion Sensors

Catalog #	Description	Wt.
SO	Sensor only, 1500w INC capacity, 120V, bronze	.7 lbs
SO-W	Sensor only, 1500w INC capacity, 120V, white	.7 lbs
S2LH	Sensor, twin 150w lampholders, coverplate, bronze	1.7 lbs
S2LH-W	Sensor, twin 150w lampholders, coverplate, white	1.7 lbs
MO	Sensor only, 500w INC capacity, 120V, bronze	.5 lbs
MO-W	Sensor only, 500w INC capacity, 120V, white	.5 lbs
M2LH	Sensor, twin 150w lampholders, coverplate, bronze	1.2 lbs
M2LH-W	Sensor, twin 150w lampholders, coverplate, white	1.2 lbs
R2LHQ	Sensor, twin 75w quartz decorative lampholders and coverplate, bronze, lamps included	1.5 lbs
R2LHQ-W	Sensor, twin 75w quartz decorative lampholders and coverplate, white, lamps included	1.5 lbs



Motion Sensors for security and welcome lighting. S Series units have wide 270° field and kits have aluminum lampholders and cover. Center focal range is 50-75 feet. M Series has 130° detection field, 40 foot center range and non-metallic lampholders and cover. Sensor has 1/2" knuckle mount, adjustable time on and sensitivity controls. Bronze or white finish. UL listed for wet locations.



Quartz motion sensors. Attractive security floodlight set. Powerful 75w G8 quartz floods controlled by 130° motion sensor so you save energy – lights only when you need it!



Louverlights

Catalog #	Description	Wt.
587M-VG	Two Tier, 60w max 120V, verdi	2.75 lbs
583M-VG	Three Tier, 100w max 120V, verdi	3.25 lbs
GP12BL	Ground post with stabilizers, non-metallic, black	2.50 lbs



Louverlights illuminate and accent walkways, driveways and flower beds. Metal construction, verdi finish, frosted glass globes for source brightness reduction, 1/2" hub, UL wet location listed.



Ground post, PVC construction with 4 stabilizers and cap.



Lampholders

Catalog #	Description	Wt.
101-B	Unshielded, 150w max, 120V, bronze	0.5 lbs
103-71	Shielded, 150w max, 120V, bronze	1.25 lbs
103-74	Shielded, 150w max, 120V, white	1.25 lbs
309-M51-ML	Deep shielded, 150w max, 120V, bronze	3 lbs
309-M54-ML	Deep shielded, 150w max, 120V, white	3 lbs



Cast aluminum units with protective powder paint finish. A variety of unshielded, shielded, and deeply shielded designs for various application requirements. 1/2" cast aluminum swivel knuckle mounting. For use in wet locations. Universal aiming capability. Use PAR lamps outdoors (309 Series can use PAR or BR lamps outdoors).



Decorative Perimeter Wallpack



NRG207B

NRG204B-MS

Catalog #	Description	Wt.
NRG207B	70w HPS, 120V, bronze	5 lbs
NRG207B-PC	70w HPS, 120V, PC, bronze	5 lbs
NRG250B	50w PS, 120V, bronze	6.5 lbs
NRG250B-PC	50w PS, 120V, PC, bronze	6.5 lbs
NRG204B	42w CFL, 120-277V, bronze	4.2 lbs
NRG204B-PC	42w CFL, 120V, PC, bronze	4.2 lbs
NRG204B-MS	42w CFL, 120V, motion sensor, bronze	5 lbs
NRG206B-PC	26w CFL, 120V, PC, bronze	4.2 lbs

Decorative, vandal resistant wallpack for typical mounting heights of 6-10ft. Curved polycarbonate face with frosted ribbed lens diffuses the light source and provides uniform distribution. Bronze finish painted inside the polycarbonate for lasting appearance. HPS, PSMH and instant-on CFL. PC units provide 120V dusk-to-dawn automatic cutoff for energy savings. Motion sensor option. Mounts over recessed junction boxes or wires to surface conduit through bottom 1/2" knockout (except MS unit). Lamps included, listed to UL1598 for use in wet locations.



Perimeter Wallpack



NRG301B

NRG304B-MS



NRG310LU

NEW
NEW

Catalog #	Description	Wt.
NRG301B	50w HPS, 120V, bronze	5 lbs
NRG301B-PC	50w HPS, 120V, PC, bronze	5 lbs
NRG307B	70w HPS, 120V, bronze	5 lbs
NRG307B-PC	70w HPS, 120V, PC, bronze	5 lbs
NRG350B	50w PS, 120V, bronze	6.5 lbs
NRG350B-PC	50w PS, 120V, PC, bronze	6.5 lbs
NRG304B	42w CFL, 120/208/240/277V, bronze	4.2 lbs
NRG304B-PC	42w CFL, 120V, PC, bronze	4.2 lbs
NRG304B-PC-W	42w CFL, 120V, PC, white	4.2 lbs
NRG304B-MS	42w CFL, 120V motion sensor, bronze	5 lbs
NRG306B	26w CFL, 120/208/240/277V, bronze	4.2 lbs
NRG306B-PC	26w CFL, 120V, PC, bronze	4.2 lbs
NRG306B-PC-W	26w CFL, 120V, PC, white	4.2 lbs
NRG310LU	10w LED, 120-277V, bronze	5 lbs
NRG310LU-PC	10w LED, 120V, PC, bronze	5 lbs

Polycarbonate front provides wide lateral spread and vandal resistance. Lateral coverage is five times the typical 6-10' mounting height. Now available in long life, energy-saving 10w LED! HID units are available in Bronze finish, White available on CFL-PC units. Photocontrol units provide dusk-to-dawn energy management. New motion sensing unit saves energy – illuminates only when needed. Cast aluminum back housing provides solid mounting to wall or recessed wiring boxes. 1/2" bottom conduit knockout allows surface conduit wiring. For use in wet locations. Lamp included.



Compact Refractor Wallpack



WGH70H	70w PS, 120/208/240/277V, glass refractor, bronze	9 lbs
WGH100H	100w PS, 120/208/240/277V, glass refractor, bronze	10 lbs
WPH70S	70w HPS, 120V, polycarbonate refractor, bronze	9 lbs
WPH100S	100w HPS, 120V, polycarbonate refractor, bronze	9 lbs

Cast aluminum housing and door with glass refractor on pulse start units. Cast aluminum housing and polycarbonate refractor on vandal-resistant HPS units. Coverage is four times the 8-12' typical mounting height. 1/2" conduit hubs allow surface wiring and field installation of photocontrols. Back hub wires to standard 4" recessed outlet boxes. Dark bronze finish. Designed for use in wet locations. Lamp included.



Mid-size Refractor Wallpack



WGH150P ¹	150w PS, 120/208/240/277V, bronze	19 lbs
WGH150S ²	150w HPS, 120/208/240/277V, bronze	18 lbs
WGH150S120 ²	150w HPS, 120V, NPF, bronze	15 lbs
WGH84F	2 x 42w FLU, 3500K, 120-277V, bronze	10 lbs

1- Medium base
2- Mogul base

Cast aluminum housing and door for rugged mounting and protection of internal components. Non-yellowing glass refractor with coverage of four times mounting height laterally and two mounting heights forward. Typical mounting height is 12-15'. 1/2" conduit hubs on sides for surface conduit and top hub allows field installation of photocontrol. Back hub allows wiring access to recessed wiring boxes. Dark bronze finish. For use in wet locations. Lamp(s) included.



Large Refractor Wallpack



WGH250P	250w PS, 120/208/240/277V, bronze	34 lbs
WGH320P	320w PS, 120/208/240/277V, bronze	37 lbs
WGH400P	400w PS, 120/208/240/277V, bronze	37 lbs
WGH250S	250w HPS, 120/208/240/277V, bronze	36 lbs
WGH400S	400w HPS, 120/208/240/277V, bronze	40 lbs

Cast aluminum housing and door with protective dark bronze powder paint for lasting appearance. Glass refractor spreads output for coverage four times laterally and two times forward of typical 18-25' mounting height. 1/2" conduit hubs on side allow surface conduit wiring. Top hub allows location for field installed photocontrol. Back hub provides wiring access to recessed wiring boxes. For use in wet locations. Lamp included.



Full Cut-off Wallpacks



NEW	LNC-5LU-5K	13w LED, 120/208/240/277V, bronze	4 lbs
NEW	LNC-5LU-5K-PC	13w LED, 120V, PC, bronze	4 lbs

New compact architectural LED wallpack produces 750 lumens while consuming only 12.6w of energy. With a 4 to 1 spacing to mounting height ratio, the Laredo LNC is not only small but requires fewer fixtures to illuminate an entry or perimeter area. The accessory acrylic diffuser (included) is designed for applications near entryways. A photocontrol is available for energy-saving dusk-to-dawn applications. 5000K. Mounts over recessed junction boxes or wires to surface conduit through bottom 1/2" knockout for quick, versatile installation.



Full Cut-off Wallpacks



Compact Series - Medium Base Socket			
NEW	WGC42F	42w CFL, 120/208/240/277V, bronze	8 lbs
	WGC50H	50w PS, 120/277V, bronze	10 lbs
	WGC70H	70w PS, 120/208/240/277V, bronze	11 lbs
	WGC100H	100w PS, 120/208/240/277V, bronze	12 lbs
	WGC100S	100w HPS, 120/208/240/277V, bronze	12 lbs

Fixture features total shielding at various mounting heights. Cast aluminum construction with stippled glass lens for lamp diffusion. Full cutoff shielding for environmentally-friendly distribution. Lateral coverage is three times typical mounting height of 8-15'. 1/2" hubs allow surface conduit wiring or access to wiring boxes. Top hub allows easy field installation of photocontrol. Dark bronze finish. For use in wet locations. Lamp(s) included.
(Shield can be removed if greater forward illumination is needed and local lighting codes allow.)



Full Cut-off Compact Wallpacks



NEW	WGM-100P	100w PS, 120/208/240/277V, bronze	18 lbs
NEW	WGM-150P	150w PS, 120/208/240/277V, bronze	19 lbs
NEW	WGM-150S	100w HPS, 120/208/240/277V, bronze	18 lbs
NEW	WGM-84F	2x42w CFL, 120-277V 60/50hz, bronze	16 lbs
NEW	WGM-84F-MS42	2x42w CFL, 120-277V 60/50hz, bronze Motion sensor	16 lbs

Dark Sky friendly, full cut-off wallpack designed for entry and perimeter lighting for 10'-15' mounting heights. Die-cast aluminum housing and door provide rigid mounting to wall; Motion sensor (MS42) detects heat change (passive infrared) in 180° radius, factory installed, controls one lamp for 50% energy savings when no activity is detected; can be easily converted in the field to 100% motion controlled if desired, motion sensor is 120V only



Full Cut-off Compact Wallpacks



NEW	WGL-250P	250w PS, 120/208/240/277V, bronze	27 lbs
NEW	WGL-250S	250w HPS, 120/208/240/277V, bronze	32 lbs
NEW	WGL-320P	320w PS, 120/208/240/277V, bronze	28 lbs
NEW	WGL-400P	400w PS, 120/208/240/277V, bronze	30 lbs
NEW	WGL-400S	400w HPS, 120/208/240/277V, bronze	32 lbs

Dark Sky friendly, full cut-off wallpack designed for entry and perimeter lighting for 15'-25' mounting heights. Die-cast aluminum housing and door, provides rigid mounting to wall; dissipates fixture heat for long component life and protection from the elements.



Full Cut-off Compact Wallpacks



	NRG-1111-B	100w PS, 120/277/347V, bronze	12 lbs
	NRG-1111-W	100w PS, 120/277/347V, white	12 lbs
	NRG-1143-B	42w CFL, 120-277V 60/50hz, bronze	7 lbs
	NRG-1143-W	42w CFL, 120-277V 60/50hz, white	7 lbs

Dark Sky friendly, decorative styling with rugged, one-piece polycarbonate front that resists rocks and other small projectiles. No uplight, energy saving. Use for wall perimeter or entry at mounting heights of 8'-12'. Listed to UL 1598 for use in wet locations.



Vandal Resistant Surface Squares



Catalog #	Description	Wt.
Compact 9" Square		
S9-42F	42w CFL, 120/208/240/277V, white	4.0 lbs
S9-70H	70w PS, 120/208/240/277V, bronze	4.5 lbs
S9-70S	70w HPS, 120/208/240/277V, bronze	4.5 lbs
Compact 12" Square		
S12-84F	2x42w CFL, 120/208/240/277V, white	8.0 lbs
S12-100H	100w PS, 120/208/240/277V, bronze	6.0 lbs
S12-150P	150w PS, 120/208/240/277V, bronze	6.75 lbs
S12-150S	150w HPS, 120/208/240/277V, bronze	7.0 lbs

Two series of surface mount units for ceiling or wall with wattage range from 42-150w. Rugged cast aluminum housing with vandal-resistant polycarbonate refractor. Typical mounting height is 8'-15' with spacing of 10'-20'. 1/2" conduit hubs on two sides allow surface conduit wiring on HID units. Top hub allows access to recessed junction boxes. Medium base sockets. Dark bronze protective finish. Designed for use in wet locations.

Low profile fluorescent units mount to recessed boxes only. (No conduit hubs available) Lamp(s) included.



DUSK-TO-DAWN

Dusk-to-Dawn



Catalog #	Description	Wt.
DD-70S*	Direct wall mount, 70w HPS screw-on 9" optic, acrylic refractor, lamp	4.0 lbs
DDS-70S	24" aluminum arm mount, 70w HPS screw-on 12" optic, acrylic refractor, lamp	4.5 lbs
DDS-100S	24" aluminum arm mount, 100w HPS screw-on 12" optic, acrylic refractor, lamp	4.5 lbs
DDS-150S	24" aluminum arm mount, 150w HPS screw-on 12" optic, acrylic refractor, lamp	5.0 lbs
DDS-70P	Same as above except 70w Pulse Start	6.0 lbs
DDS-100P	Same as above except 100w Pulse Start	6.0 lbs
DDS-65F	Same as above except 65w CFL	4.0 lbs

Security luminaires provide large area coverage and dusk-to-dawn energy saving control. Units are an exceptional value as kits, complete with lamps, photocontrol and mounting hardware. DDS kits include curved 24" aluminum arm. All units are 120V. Units are UL approved for use in wet locations.



*Subject to availability, arm not included

INDUSTRIAL

Industrial Highbay/Lowbay



Catalog #	Description	Wt.
BL-400P-HB	Highbay, 400w PS, 120/208/240/277V, white	24 lbs
BL-400P-HB-Q	Highbay, 400w PS, 120/208/240/277V, w/ Quartz restrrike, white	24 lbs
BL-400P-LB	Lowbay, 400w PS, 120/208/240/277V, white	24 lbs
BL-400P-LB-Q	Lowbay, 400w PS, 120/208/240/277V, w/ Quartz restrrike, white	24 lbs

Ruggedly built industrials with cast aluminum ballast housing for heat dissipation and long ballast life. Cast aluminum safety hook included. 3/4" top hub on easy wire box. 400w pulse start metal halide lamp included. 16" diameter optics. Glass lens provided on BL-400PHB, drop acrylic on BL-400PLB. Typical mounting height: Highbay 18'-25'/Lowbay 14'-20'. Quartz restrrike units are available. (Quartz lamp included)



Vaportites



Catalog # Description

Wt.

VBGG-150	Box, Pendant, 150w max, 120V
VBGG-300	Box, Pendant, 300w max, 120V
VWGG-150	Wall mount with box, 150w max, 120V
VWGG-300	Wall mount with box, 300w max, 120V

3.0 lbs	Rugged die cast aluminum, clear globe and guard, wet location listed Vaportites for ceiling or pendant and wall mount. Two sizes handle wattages from 20 to 300w. Lamps not included. Use for entry, corridors, tunnels, service passages, stairwells. Platinum silver finish.
3.5 lbs	
4.0 lbs	
4.5 lbs	



Universal LED Exit Signs



Catalog # Description

Wt.

ECSXWREB3	Exit, Red Letters, White 120/277
ECSXWGEB3	Exit, Green Letters, White 120/277

2.6 lbs	Universal mount with single or double face White thermoplastic housing. 120/277VAC Red or Green letter units, damp location listed.
2.6 lbs	

Emergency Units



ECSEU1	Fixed Head, Halogen 5.4 w Lamps, White
ECSEU2	Adjustable Head, Halogen 5.4 w Lamps, White

3.3 lbs	Fixed or adjustable head units with white housing. Sealed-maintenance free batteries fully automatic, test switch and LED charge Indicator. 120/277VAC, damp location listed.
4.2 lbs	



Combo Exit Signs



ESMXWR3	Combo Exit, Universal, Red Letters
ESMXWG3	Combo Exit, Universal, Green Letters

7.7 lbs	LED single or double face exit sign with adjustable side mount lighting heads. Ceiling or wall mount. White finish with red or green letter selections. 120/277VAC, damp location listed.
7.7 lbs	

Tulip



	Catalog #	Description	Wt.
NEW	TL-AB	Tulip 1.5w LED, Antique bronze	2.3
NEW	TL-AG	Tulip 1.5w LED, Antique green	2.3

The plant lover's favorite. Sweeping stem tulip, 20" tall with decorative leaves. Use along paths, walkways or to accent special planting. Creates a 6' pool of light with forward throw. Needs little or no watering!

Mission



	Catalog #	Description	Wt.
NEW	MS-AB	Mission 1.5w LED, Antique bronze	3.3
NEW	MS-AG	Mission 1.5w LED, Antique green	3.3

Traditional and classic. Complements a wide variety of architecture. Soft glow to side and ground. Stands 16" tall with 5" square head. Typical spacing 8'-10'.

Seashell



	Catalog #	Description	Wt.
NEW	SS-AB	Seashell 1.5w LED, Antique bronze	2.0
NEW	SS-AG	Seashell 1.5w LED, Antique green	2.0

Large seashell with adjustable knuckle. Use as full cut-off or tilt up (45° max.) for larger area coverage. A powerful and flexible luminaire for lighting large flower beds or plantings around building perimeters.

Greenville



	Catalog #	Description	Wt.
NEW	GN-AB	Greenville 1.5w LED, Antique bronze	2.8
NEW	GN-PT	Greenville 1.5w LED, Platinum silver	2.8

A stately appearance with classic shape. Stands 17" tall with 5" diameter head. Frosted glass lens provides soft lighting of taller surrounding plantings with 5' coverage. Use along walkways, steps. Typical spacing 8'-12'.

Saturn



	Catalog #	Description	Wt.
NEW	SA-AB	Saturn 1.5w LED, Antique bronze	2.8
NEW	SA-PT	Saturn 1.5w LED, Platinum silver	2.8

Modern and distinctive shepherd's crook with rotatable arm. Decorative copper-top head and cone shape frosted glass lens. Lighting covers 6' circle with ample vertical illumination for taller plantings. Make a statement with Saturn!

Cone



	Catalog #	Description	Wt.
NEW	CO-AB	Cone 1.5w LED, Antique bronze	2.0
NEW	CO-AG	Cone 1.5w LED, Antique green	2.0

Create a tropical image. The basic 7" diameter cone shape sits 16" high and creates a 5' lighted area with soft, indirect shielded light. Excellent for subtle illumination of plants or walkways.

Reidville

Catalog # Description Wt.



NEW	RD-AB	Reidville 1.5w LED, Antique bronze	3.3
NEW	RD-PT	Reidville 1.5w LED, Platinum silver	3.3

Bell-shaped head supported by decorative arm and sturdy staff. Full cut-off pattern provides 5' pool of light on ground with no glare. Perfect for highlighting walkways, flowers and plants. Typical spacing 8'-10'.

Flood

Catalog # Description Wt.



NEW	FL-AB	Flood 3w LED, Antique bronze	2.0
------------	--------------	------------------------------	-----

Powerful 3w LED projection flood with adjustable knuckle for versatile aiming. Use for accent lighting of building facades, small signs or address numbers, columns, trees and residential flags to 20' height.

Eyelid

Catalog # Description Wt.



NEW	EL-AB	Eyelid 1.5w LED, Antique bronze	1.0
NEW	EL-PT	Eyelid 1.5w LED, Platinum silver	1.0

Round 4" diameter eyelid for deck post or steplighting. Can be surface mounted or semi-recessed. Use for accent or small area illumination of perimeters or stairways. 2' mounting height provides soft coverage 5' wide, 2' forward.

Recessed

Catalog # Description Wt.



NEW	RE-PT	Recessed 3w LED, Pewter	1.5
------------	--------------	-------------------------	-----

Round recessed uplight for accent lighting of trees, columns and building facades. Powerful 3W LED projection beam. Provides hidden light source.

Transformer & Wiring

Catalog # Description Wt.



NEW	LVT56	56w low voltage transformer with PC	4.0
NEW	CB-75	75' 14 gauge low energy cable	6.0
NEW	CB-150	150' 14 gauge low energy cable	4.0

Non-metallic case protects timer controls and 120V-to-12V transformer. Surge protected with grounded cord/plug set and easy 12V cable attachment. Photocontrol triggers "time-on", eliminating seasonal adjustment. UL and c-UL certified (Controls 15 3w or 30 1.5w fixtures)

Low voltage #14 cable runs from LVT56 control center down path of lighting. UV protected, burial is not required, hide with mulch if desired. Perfect fit with fixture connectors for easy installation.

Accessories included with fixtures



STAKE
8" black die-cast aluminum stake with set screw and epoxy outer coating.



FLAT SURFACE CONNECTOR
Each stake mounted fixture includes flat surface mount with two phillips head screws. Allows mounting to deck, steps or wood walkway.



"SMART CONNECT"
Easy to install tool-free connector allows flexibility of fixture layouts. Select a central location and attach smart connector to main 12V cable with 4 ft. fixture cable. As plants and vegetation grow, fixture can be moved within an 8' diameter from existing connection.

WE'RE READY TO HELP YOU MAXIMIZE SALES!

**6' MERCHANDISING WIRE GONDOLA DISPLAY (EXPRESSLINE OR EXPRESSCAPE)
(EXP-LS)**

**12V LED LIGHTSCAPER DISPLAY
(EXP-SR)**



**CONTRACTOR
CASH BACK HOLDER
AVAILABLE**

Hubbell Lighting Inc. Distinguished Lighting Brands

Alera Lighting
Architectural Area Lighting
Beacon Products
Columbia Lighting
Compass Products
Devine Lighting
Dual-Lite
HomeStyle Lighting
Hubbell Building Automation
Hubbell Industrial Lighting
Hubbell Outdoor Lighting



Kim Lighting
Kurt Versen
Prescolite
Progress Lighting
Security Lighting
Spaulding Lighting
Sportsliter Solutions
Sternner Lighting Systems
Thomasville Lighting
Whiteway

United States
Hubbell Lighting, Inc.
701 Millennium Boulevard
Greenville, SC 29607
864-678-1000

Canada
Hubbell Canada
870 Brock Road
Pickering, Ontario L1W 1Z8
www.hubbell-canada.com

Mexico
Hubbell De Mexico, S.A. DE.CV
Av. Insurgentes Sur # 1228, 8th Floor
Col. Tlacoquemecatl del Valle • 03200 Mexico, D.F.
www.hubbell.com.mx

Due to our continued efforts to improve our products, product specifications are subject to change without notice.