

Conduit Body Covers

Malleable Iron Covers and Neoprene Gaskets

Application:

- Used with conduit bodies to cover opening.

Features:

- Supplied with Stainless Steel captive screws
- Sizes 2 1/2" thru 4" with raised dome affords additional wiring room

Standard Materials:

Malleable Iron

Standard Finish:

Zinc plated



UL Listed:
E208392

Application:


- Gasket used with conduit bodies for a raintight seal.

Standard Materials:

Neoprene Rubber




Type 01M



| CATALOG NUMBER | TRADE SIZE | DIM A | DIM B | DIM C | UNIT PACK | STANDARD PACK | WEIGHT (LBS.) PER 100 PCS. | NAED MFG #78-5994 UPC/DCI # |
|-----------------------|-----------------|--------|-------|-------|-----------|---------------|----------------------------|-----------------------------|
| Malleable Iron | | | | | | | | |
| 01M | 1/2" | 3.936 | 1.313 | 0.063 | 25 | 250 | 23 | 90131 |
| 02M | 3/4" | 4.625 | 1.500 | 0.063 | 25 | 250 | 31 | 90132 |
| 03M | 1" | 5.313 | 1.750 | 0.063 | 20 | 200 | 41 | 90133 |
| 04M | 1-1/4" - 1-1/2" | 7.188 | 2.500 | 0.250 | 25 | 100 | 91 | 90134 |
| 05M | 2" | 9.500 | 3.188 | 0.313 | - | 25 | 208 | 90135 |
| 06M | 2-1/2" - 3" | 12.125 | 4.313 | 1.063 | - | 10 | 358 | 90136 |
| 07M | 3-1/2" - 4" | 14.875 | 5.625 | 1.125 | - | 10 | 550 | 90137 |



Type 11



| CATALOG NUMBER | TRADE SIZE | DIM A | DIM B | UNIT PACK | STANDARD PACK | WEIGHT (LBS.) PER 100 PCS. | NAED MFG #78-5994 UPC/DCI # |
|-------------------------|-----------------|-------|-------|-----------|---------------|----------------------------|-----------------------------|
| Neoprene Gaskets | | | | | | | |
| 10 | 1/2" | 3.90 | 1.37 | 200 | 2000 | 3 | 49910 |
| 11 | 3/4" | 4.60 | 1.56 | 100 | 1000 | 3 | 49911 |
| 12 | 1" | 5.34 | 1.73 | 100 | 1000 | 3 | 49912 |
| 13 | 1-1/4" - 1-1/2" | 7.25 | 2.51 | 50 | 500 | 6 | 49913 |
| 14 | 2" | 9.50 | 3.05 | 25 | 100 | 11 | 49914 |
| 15 | 2-1/2" - 3" | 12.13 | 4.39 | - | 10 | 13 | 49915 |
| 16 | 3-1/2" - 4" | 14.88 | 5.43 | - | 10 | 28 | 49916 |