

## DATA/VOICE CABLE

**Cat6e -Enhanced Category 6**  
**4 Pair -23 AWG -550 MHz.**  
**CMR UTP Cable**



CONSTRUCTION	
Construction	- Solid bare copper
Insulation	- High Density Polyethylene (HDPE)
Pairing	- Varying short pair lay
Jacket	- Flame-retardant PVC

### Applications:

- High Speed Horizontal Cabling
- 100 Mbps TPDDI
- 1000 Base T
- 622 Mbps ATM
- IEEE 802.3
- IEEE 802.5
- Digital Video

### Standards:

- EIA/TIA 568
- ISO/IEC 11801
- ETL/UL Available

Part #	AWG	Pairs	Nom. O.D.	Lbs./M'
J562304-XX	23	4	.236"	32

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

Insert the color number in the -XX location:

- 01 = Black
- 02 = White
- 03 = Red
- 04 = Green
- 05 = Blue
- 06 = Gray
- 07 = Orange
- 08 = Yellow
- 09 = Purple
- 11 = Pink

COLOR CODE CHART	
Pairs	Color
1	Blue & White/Blue Stripe
2	Orange & White/Orange Stripe
3	Green & White/Green Stripe
4	Brown & White/Brown Stripe