



# SWITCHES


## TradeMaster® Decorator Switches 15A, 120/277VAC



TM870LA



TM873LA



TM874LA

### Features

- Designer-style satin-finish rocker.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.
- Extra-long, through-body strap eliminates floating installations and imperfect applications.
- Smooth, quiet paddle action.
- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.
- ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.


CATALOG NUMBER	RATING		COLOR	3rd PARTY COMPLIANCE		
	A.	V.		UL20	UL US	C22.2 111
<b>SINGLE POLE DECORATOR SWITCHES GROUNDING</b>						
TM870I	15	120/277	Ivory	•		•
TM870W	15	120/277	White	•		•
TM870	15	120/277	Brown	•		•
TM870GRY	15	120/277	Gray	•		•
TM870BK	15	120/277	Black	•		•
TM870LA	15	120/277	Light Almond	•		•
TM870NICC10	15	120/277	Nickel	•		•
TM870TI	15	120/277	Titanium	•		•
<b>NAFTA-COMPLIANT SINGLE POLE DECORATOR SWITCHES GROUNDING</b>						
TM870NAI	15	120	Ivory		•	
TM870NAW	15	120	White		•	
TM870NA	15	120	Brown		•	
TM870NAGRY	15	120	Gray		•	
TM870NABK	15	120	Black		•	
TM870NALA	15	120	Light Almond		•	
TM870ABCC10	15	120	Antique Brass		•	
TM870DBCC10	15	120	Dark Bronze		•	
<b>THREE-WAY DECORATOR SWITCHES GROUNDING</b>						
TM873I	15	120/277	Ivory	•		•
TM873W	15	120/277	White	•		•
TM873	15	120/277	Brown	•		•
TM873GRY	15	120/277	Gray	•		•
TM873BK	15	120/277	Black	•		•
TM873LA	15	120/277	Light Almond	•		•
TM873NICC10	15	120/277	Nickel	•		•
TM873TI	15	120/277	Titanium	•		•
<b>NAFTA-COMPLIANT THREE-WAY DECORATOR SWITCHES GROUNDING</b>						
TM873NAI	15	120	Ivory		•	
TM873NAW	15	120	White		•	
TM873NA	15	120	Brown		•	
TM873NAGRY	15	120	Gray		•	
TM873NABK	15	120	Black		•	
TM873NALA	15	120	Light Almond		•	
TM873ABCC10	15	120	Antique Brass		•	
TM873DBCC10	15	120	Dark Bronze		•	
<b>FOUR-WAY DECORATOR SWITCHES GROUNDING</b>						
TM874I	15	120/277	Ivory	•		•
TM874W	15	120/277	White	•		•
TM874	15	120/277	Brown	•		•
TM874BK	15	120/277	Black	•		•
TM874LA	15	120/277	Light Almond	•		•
TM874NICC6	15	120/277	Nickel	•		•
TM874TI	15	120/277	Titanium	•		•
<b>NAFTA-COMPLIANT FOUR-WAY DECORATOR SWITCHES GROUNDING</b>						
TM874I	15	120	Ivory		•	
TM874W	15	120	White		•	
TM874	15	120	Brown		•	
TM874BK	15	120	Black		•	
TM874LA	15	120	Light Almond		•	
TM874ABCC10	15	120	Antique Brass		•	
TM874DBCC10	15	120	Dark Bronze		•	

NAFTA-Compliant Switches are ideal for use on projects subject to the provisions of the Buy American Act.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# SWITCHES

## TradeMaster® Decorator Illuminated & Self-Grounding Switches 15A, 120 & 120/277VAC


**TM870LASL**
**TM870SLA**

### Features

- Designer-style satin-finish rocker.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.
- Extra-long, through-body strap eliminates floating installations and imperfect applications.
- Smooth, quiet paddle action.
- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.
- Self-grounding models provide automatic ground clip.

CATALOG NUMBER	RATING		COLOR	3rd PARTY COMPLIANCE	
	A.	VAC		UL20	C22.2 111
<b>SINGLE POLE ILLUMINATED DECORATOR SWITCHES GROUNDING (LIGHTED WHEN OFF)</b>					
TM870ISL	15	120	Ivory	•	•
TM870WSL	15	120	White	•	•
TM870LASL	15	120	Light Almond	•	•
<b>SELF-GROUNDING SINGLE POLE DECORATOR SWITCHES</b>					
TM870SI	15	120/277	Ivory	•	•
TM870SW	15	120/277	White	•	•
TM870S	15	120/277	Brown	•	•
TM870SBK	15	120/277	Black	•	•
TM870SLA	15	120/277	Light Almond	•	•
<b>THREE-WAY ILLUMINATED DECORATOR SWITCHES GROUNDING (LIGHTED WHEN OFF)</b>					
TM873ISL	15	120	Ivory	•	•
TM873WSL	15	120	White	•	•
TM873LASL	15	120	Light Almond	•	•
<b>SELF-GROUNDING THREE-WAY DECORATOR SWITCHES</b>					
TM873SI	15	120/277	Ivory	•	•
TM873SW	15	120/277	White	•	•
TM873S	15	120/277	Brown	•	•
TM873SBK	15	120/277	Black	•	•
TM873SLA	15	120/277	Light Almond	•	•
<b>FOUR-WAY ILLUMINATED DECORATOR SWITCHES GROUNDING (LIGHTED WHEN OFF)</b>					
TM874ISL	15	120	Ivory	•	•
TM874WSL	15	120	White	•	•
TM874LASL	15	120	Light Almond	•	•
<b>SELF-GROUNDING FOUR-WAY DECORATOR SWITCHES</b>					
TM874SI	15	120/277	Ivory	•	•
TM874SW	15	120/277	White	•	•
TM874S	15	120/277	Brown	•	•
TM874SBK	15	120/277	Black	•	•
TM874SLA	15	120/277	Light Almond	•	•


All devices listed on this page conform to NEMA WD-1 and WD-6.




# SWITCHES

## Decorator & Specification Grade Momentary & Maintained Contact Switches


15A, 120 & 120/277VAC



TM870STMLACC6



Momentary Contact



Maintained Contact

### Features

- Designer-style satin-finish rocker.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.
- Extra-long, through-body strap eliminates floating installations and imperfect applications.
- Smooth, quiet paddle action.
- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.

CATALOG NUMBER	RATING		COLOR	3rd PARTY COMPLIANCE	
	A.	VAC		UL20	C22.2 111
<b>SINGLE POLE DECORATOR MOMENTARY CONTACT SWITCHES</b>					
TM870STMWCC6	15	120/277	White	•	•
TM870STMBKCC6	15	120/277	Black	•	•
M870STMLACC6	15	120/277	Light Almond	•	•


### Features

- Unique "Up/Down" switches match the look and feel of standard decorator switches.
- Impact-resistant face and body.
- Side and external screw-pressure-plate back wire accepts #12 and #14 AWG.
- All screws are tri-drive.
- Full wraparound heavy-gauge steel strap is plated for corrosion resistance and features lock-in tabs.
- Patent-pending split circuit tab – easily accessible, and can be reinstalled without a tool.

CATALOG NUMBER	RATING		COLOR	3rd PARTY COMPLIANCE		
	A.	VAC		cULus	UL20	UL508
<b>SPECIFICATION GRADE DOUBLE THROW MOMENTARY CONTACT SWITCHES</b>						
TM811DTMOI	15	120	Ivory	•		•
TM811DTMOW	15	120	White	•		•
TM811DTMOBK	15	120	Black	•		•
TM811DTMOLA	15	120	Light Almond	•		•
<b>SPECIFICATION GRADE DOUBLE THROW MAINTAINED CONTACT SWITCHES</b>						
TM811DTMAI	15	120	Ivory	•	•	
TM811DTMAW	15	120	White	•	•	
TM811DTMABK	15	120	Black	•	•	
TM811DTMALA	15	120	Light Almond	•	•	

# SWITCHES

## Specification Grade Decorator Combination Switches & Shim-Lock 20A, 277VAC



### 15 & 20 Amp

#### Features


- Unique "Up/Down" switches match the look and feel of standard decorator switches.
- Impact-resistant face and body.
- Side and external screw pressure plate back wire accepts #12 and #14 AWG.
- All screws are tri-drive.
- Full wraparound heavy-gauge steel strap is plated for corrosion resistance and features lock-in tabs.
- Patent-pending split circuit tab – easily accessible, and can be reinstalled without a tool.
- Patent-pending snap-in light module (sold separately) transforms a combination switch into an illuminated switch.
- Identification modules (sold separately) identifies each switch – light, fan heat lamp. See Page A-24 for details.

CATALOG NUMBER	RATING		COLOR	3rd PARTY COMPLIANCE	
	A.	VAC		ULus cULus	UL UL20
<b>TWO SINGLE POLE SWITCHES</b>					
PS81120I	20	277	Ivory	•	•
PS81120W	20	277	White	•	•
PS81120LA	20	277	Light Almond	•	•
<b>THREE SINGLE POLE SWITCHES</b>					
PS811120I	20	277	Ivory	•	•
PS811120W	20	277	White	•	•
PS811120LA	20	277	Light Almond	•	•
<b>SNAP-IN LIGHT MODULE*</b>					
PS8LM	—	—	Clear		

\*For use with PS81120 and PS811120 only.



Shim-Lock



#### Features

- One Shim-Lock provides a device adjustment depth range between 1/8" and 3/4".
- An inexpensive and quick fix for floating installations.
- Provides a perfect flush mount every time regardless of the wallboard, tile or panel condition.
- Made of steel and finished with clear zinc chromate plating.

CATALOG NUMBER	DIMENSIONS	QTY. PER PACKAGE
<b>SHIM-LOCK</b>		
SHL20	Length: .310", Screw Opening: #6	20
SHL100	Length: .310", Screw Opening: #6	100

# SWITCHES


## TradeMaster® Decorator Combination Switches



### TM8113WCC

#### PlugTail™ Decorator Combination Switches

- A. Unique “Up/Down” switches** match the look and feel of standard Decorator switches.
- B. Easy-to-use oversized main switch** for primary load.
- C. Patented Snap-In Light Module** (sold separately) transforms a combination switch into an illuminated switch in seconds.
- D. Impact-resistant face and body.**
- E. Ground screw position under the end of the strap** minimizes the risk of contact.
- F. Full wraparound metal strap**, commercial grade with lock-in tabs.
- G. All screws are tri-drive.**
- H. Patented split circuit tab** – easily accessible, and can be reinstalled without a tool.
- I. External screw-pressure-plate back and side wired.** Accepts #12 and #14 AWG.
- J. Fully rounded back body** protects wires from being damaged by sharp edges.



**Identification modules** (sold separately) identifies each switch — light, fan, heat lamp.

Shown with Snap-In Light Module TM8LMCC.


### Features

- Module simply snaps-in for easy installation.
- Can be installed with the following devices: TM811, TM813, TM833, TM818, TM838, TM8111, TM8113, TM81111, TM8118, and the LS Series of Dimmers & Fan Speed Controls (see Pages L-14 through L-16).

#### Snap-In Light Module:

- Lights when OFF.
- Uses energy-efficient 1/4 watt LED light.
- LED light will not generate heat and will last on average 47 years.


CATALOG NUMBER	RATING		COLOR	3rd PARTY COMPLIANCE UL cULus
	A.	VAC		
<b>SNAP-IN LIGHT MODULE</b>				
TM8LMCC	15	120/125	Clear	•
<b>IDENTIFICATION MODULES</b>				
TM8IDIC	—	—	Ivory	
TM8IDWCC	—	—	White	
TM8IDCC	—	—	Brown	
TM8IDBKCC	—	—	Black	
TM8IDLACC	—	—	Light Almond	




All devices listed on this page conform to NEMA WD-1 and WD-6.

# SWITCHES


## TradeMaster® Decorator Combination Switches 15A, 120VAC



TM811WCC



TM8111WCC



TM81111WCC


### Features

- Impact-resistant face and body.
- Fully rounded back body protects wires from being damaged by sharp edges.
- Clear identification of circuits.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Full wraparound metal strap with lock-in tabs.
- Patented split circuit tab – easily accessible, and can be reinstalled without a tool.
- Unique "Up/Down" switches match the look and feel of standard Decorator switches.
- Largest breadth of 15 amp offering.
- All screws are tri-drive.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects (see Page A-26).


CATALOG NUMBER	RATING		COLOR	3rd PARTY COMPLIANCE	
	A.	VAC		UL US UL20	UL cULus
<b>TWO SINGLE POLE SWITCHES</b>					
TM811ICC	15	120	Ivory	•	•
TM811WCC	15	120	White	•	•
TM811CC	15	120	Brown	•	•
TM811BKCC	15	120	Black	•	•
TM811LACC	15	120	Light Almond	•	•
<b>SINGLE POLE SWITCH &amp; THREE-WAY SWITCH</b>					
TM813ICC	15	120	Ivory	•	•
TM813WCC	15	120	White	•	•
TM813CC	15	120	Brown	•	•
TM813BKCC	15	120	Black	•	•
TM813LACC	15	120	Light Almond	•	•
<b>TWO THREE-WAY SWITCHES</b>					
TM833ICC	15	120	Ivory	•	•
TM833WCC	15	120	White	•	•
TM833CC	15	120	Brown	•	•
TM833BKCC	15	120	Black	•	•
TM833LACC	15	120	Light Almond	•	•
<b>THREE SINGLE POLE SWITCHES</b>					
TM8111ICC	15	120	Ivory	•	•
TM8111WCC	15	120	White	•	•
TM8111CC	15	120	Brown	•	•
TM8111BKCC	15	120	Black	•	•
TM8111LACC	15	120	Light Almond	•	•
<b>TWO SINGLE POLE SWITCHES &amp; THREE-WAY SWITCH</b>					
TM8113WCC	15	120	White	•	•
TM8113BKCC	15	120	Black	•	•
<b>FOUR SINGLE POLE SWITCHES</b>					
TM81111ICC	15	120	Ivory	•	•
TM81111WCC	15	120	White	•	•
TM81111CC	15	120	Brown	•	•
TM81111BKCC	15	120	Black	•	•
TM81111LACC	15	120	Light Almond	•	•

# SWITCHES

## TradeMaster® Tamper-Resistant Decorator Combination Switches 15A, 120/125VAC



TM818TRWCC



TM838TRLACC

CATALOG NUMBER	RATING		COLOR	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE		
	A.	VAC			UL20	UL498	cULus
<b>TAMPER-RESISTANT SINGLE POLE SWITCH &amp; SINGLE RECEPTACLE</b>							
TM818TRICC	15	120/125	Ivory	5-15R	•	•	•
TM818TRWCC	15	120/125	White	5-15R	•	•	•
TM818TRCC	15	120/125	Brown	5-15R	•	•	•
TM818TRBKCC	15	120/125	Black	5-15R	•	•	•
TM818TRLACC	15	120/125	Light Almond	5-15R	•	•	•
<b>TAMPER-RESISTANT SINGLE POLE SWITCH &amp; SINGLE RECEPTACLE WITH PILOT LIGHT</b>							
TM818TRPLICC	15	120/125	Ivory	5-15R	•	•	•
TM818TRPLWCC	15	120/125	White	5-15R	•	•	•
TM818TRPLBKCC	15	120/125	Black	5-15R	•	•	•
TM818TRPLLACC	15	120/125	Light Almond	5-15R	•	•	•
<b>TAMPER-RESISTANT THREE-WAY SWITCH &amp; SINGLE RECEPTACLE</b>							
TM838TRICC	15	120/125	Ivory	5-15R	•	•	•
TM838TRWCC	15	120/125	White	5-15R	•	•	•
TM838TRCC	15	120/125	Brown	5-15R	•	•	•
TM838TRBKCC	15	120/125	Black	5-15R	•	•	•
TM838TRLACC	15	120/125	Light Almond	5-15R	•	•	•
<b>TAMPER-RESISTANT TWO SINGLE POLE SWITCHES &amp; SINGLE RECEPTACLE</b>							
TM8118TRICC	15	120/125	Ivory	5-15R	•	•	•
TM8118TRWCC	15	120/125	White	5-15R	•	•	•
TM8118TRCC	15	120/125	Brown	5-15R	•	•	•
TM8118TRBKCC	15	120/125	Black	5-15R	•	•	•
TM8118TRLACC	15	120/125	Light Almond	5-15R	•	•	•