
Page 1 of 1

5" Aperture Lyte Incandescent Convertible IC/Non-IC Remodeler Frame-In Kit



5" Aperture: Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets									
	Open Downlight					Adjustable				
	Reflector	Cone	Satin Cone	Baffles	Basic White	Eyeball	Enclosed Diffuser	Open Wet Location	Wall Washer	
1004ICR	1045 1046 1046CD	1012 1012NM 1013 1013BK 1013WH 1013NM 1013CD 1013BKNM 1013CDNM		1005 1005NM 1005BNM 1005WH 1076 1076WH	1071	1022 1022WH 1082 1088 1088GW 1088WH	1021* 1024* 1177LX 1178LX 1090*	1081CD 1081WH	1085*	

## **Features**

- Housing: .032 (#20 ga.) Aluminum. U.L. listed convertible IC/NON-IC. Integral retaining spring secures housing to ceilings up to 2" thick. Removable for access to junction box and ceiling plenum.
- 2. Junction Box: 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032 (#22 ga.) galvanized steel. U.L. listed for 90°C supply wire. Cable clamp permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors.
- **3. Socket Housing:** Impact extruded aluminum or galvanized steel. Attached trim retaining spring secures trim to any height on housing wall.
- **4. Socket:** Porcelain medium base: nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 VOLT 200°C) leads to junction box.
- Thermal Protector: Meets NEC and U.L. requirements. Located inside housing.

## Options & Accessories AirSeal® Kit: LAS56R

## Labels

UL (Type IC/NON-IC Convertible; Suitable for Damp Locations).

Romex<sup>®</sup> is a registered trademark of General Cable Industries Inc.

Туре:			

**Lightolier** a Genlyte company www.lightolier.com 631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710 We reserve the right to change details of design, materials and finish. © 2006 Genlyte Group LLC • H0314