



Complete Fixtures are available **separately.**

1003R	Open Downlight						Recessed Adjustable		Enclosed Diffusers	Wall Washer	Open Wet Location
	Reflector	Cone	Satin Cone	Baffles	Basic White	Pinhole					
	1045	1012	1008	1005	1071	1011	1027	1038	1021	1035	1084CD
	1046	1012NM	1008NM	1005WH			1027WH	1038NM	1024	1035WH	1084WH
	1046CD	1013	1010	1005NM			1027BK	1048	1078	1085	
		1013BK	1010NM	1005BNM			1027NM	1048NM	1090		
		1013WH		1076			1027BNM				
		1013CD		1076WH			1027CD				
		1013NM					1027BKNM				
		1013BKNM					1027CDNM				
		1013CDNM									
							Eyeball:				
							1022				
							1022WH				
							1082				

## Features

- Mounting Ring:** .032 (#22 ga.) galvanized steel. Accommodates existing ceilings up to 2" thick. Attaches securely to any type of ceiling material without tools using (3) mounting straps provided. Push-in/twist-out clips hold reflector flush to ceiling. Includes adhesive backed aperture template.
- Junction Box:** 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032 (#22 ga.) galvanized steel. U.L. listed for 90° C supply wire. Integral cable clamps permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors. Attaches to mounting ring without tools.
- Socket Housing:** Impact extruded aluminum or galvanized steel.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 VOLT 200° C) leads to junction box.
- Thermal Protector:** Meets NEC and U.L. requirements. Do not install insulation within 3 inches of fixture sides or wiring compartment nor above fixture in such a manner as to entrap heat.

## Labels

UL (Suitable for Damp Locations)

Romex® is a registered trademark of General Cable Industries Inc.

Job Information	Type:
<b>Job Name:</b>	
<b>Cat. No.:</b>	
<b>Lamp(s):</b>	
<b>Notes:</b>	