



Frame-in Kit



Reflector Trim

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets						
	Open Downlight			Recessed		Enclosed	Open Wet
	Aperture Cone	Baffles	Satin Cone	Adjustable	Eyeball	Diffuser	Location
2000AIC	2012 2012NM 2013 2013NM 2013BK 2013BKNM 2013CD 2013CDNM 2013WH 2013WD 2013WDP	2005 2005BNM 2005WH 2005NM	2008 2008NM 2010 2010NM	2027 2027BNM 2027NM 2027WH 2029WH 2029BK 2029BKNM 2029CD 2029CDNM 2029CLNM 2029GD 2029GDNM 2029CL	2022 2022WH	2090	2084WH 2084CD

## Features

- Housing:** .032" aluminum. UL Listed for direct contact with thermal insulation. AirSeal® Housing minimizes air leakage to less than 2 CFM at 1.57 PSF, which complies with Model Energy Code (Section 602.3.3) and the Washington State Energy Code (Section 502.4) and reduces heat loss and condensation on ceiling. Access door for inspection of junction box.
- Mounting Frame:** .036" (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- Junction Box:** 4" X 3 1/2" X 2"; .063" (#14 ga.) galvanized steel. UL listed for maximum of 4 No. 12 ga. 90° C through branch circuit conductors. Access door inside of housing allows easy inspection of wiring without removal of housing. Integral cable clamps permit attachment of nonmetallic Romex® or armored cable without need of additional connectors.
- Mounting Bars:** .059" (#16 ga.) galvanized steel. 13" long bars extend to 27" with integral nailing tabs. Attaches to wood joist without need of accessories.
- Socket Housing:** .036" (#20 ga.) galvanized steel.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 leads to junction box.
- Thermal Protector:** Meets NEC and UL requirements. Located inside housing

## Options and Accessories

- Mounting Bars:** 1964 - 20" set of (2)  
**T-Bar Ceiling Clips:** 1956 - set of (4)  
**Plaster Ceiling Ring:** 1959 - 7/8" depth for wet plaster ceilings  
**277V Remote Step Down Transformer:** 7997 - 277V down to 120V 300W max. load.  
**Extra Thick Ceiling Mounting Ring:** 1967C

## Labels

UL (Suitable for Damp Locations) I.B.E.W.

Complies with Air Leakage Requirements as stated in the Model Energy Code and the Washington State Energy Code.

AirSeal® is a registered trademark of Lightolier.

Romex® is a registered trademark of General Cable Industries Inc.

Job Information	Type:
<b>Job Name:</b>	
<b>Cat. No.:</b>	
<b>Lamp(s):</b>	
<b>Notes:</b>	

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710  
 We reserve the right to change details of design, materials and finish.  
 www.lightolier.com © 2012 Philips Group • L0112