

Electrical Markets Division  
3M™ Portable Labelers and Refill Cartridges



# Innovation That Sticks With You

manufactured by:

**DYMO**



**3M**



# 3M™ Portable Labeler Family

3M offers a family of portable labelers to tackle any number of jobs from DIY to industrial jobsite applications. All units are equipped with one-touch formatting keys that provide shortcuts for the most common formatting tasks.

The 3M™ Portable Labelers will print on a range of label materials, including heat shrink. The label cartridges are interchangeable and easy to install and remove. To get the job done quickly and effectively, choose 3M.

|                              | PL150 | PL200 | PL300 |
|------------------------------|-------|-------|-------|
| One-Touch Formatting keys    | X     | X     | X     |
| “Favorites” key              | X     |       |       |
| PC connectivity              |       |       | X     |
| Backlit LCD                  | X     | X     | X     |
| Power cutter                 |       |       | X     |
| Rubber protective bumper     | X     | X     | X     |
| Symbol library terms         | 80    | 100   | 250   |
| Bar code capability          | X     | X     | X     |
| Stores 100 labels            |       | X     | X     |
| Stores 1,000 labels          |       |       | X     |
| Prints on heat shrink        | X     | X     | X     |
| Supports labels up to 3/4"   | X     | X     | X     |
| Supports labels up to 1"     |       |       | X     |
| Offered as a kit             | X     | X     | X     |
| Rechargeable battery capable | X     | X     | X     |
| Computer-style keyboard      | X     |       |       |



# 3M™ Portable Labeler PL150

The 3M™ Portable Labeler PL150 features the same keyboard layout as your computer (QWERTY), along with one-touch hot keys which allow you to quickly create wire/cable wraps, flags, Code 39 and Code 128 barcodes, fixed-length labels, breaker labels and more.

Print labels up to 3/4" wide in flexible nylon, permanent polyester and durable vinyl materials — PLUS print directly on heat-shrink tubes. Save even more time with great new features like the "Favorites" and "Custom" keys which provide single-key access to commonly used labels, symbols and terms and eliminate repeated steps by saving customized settings. The PL150 accommodates 1/4", 3/8", 1/2" and 3/4" labels.



## Easy to Read

Large character LCD display

## Easy to See

High contrast backlight

## Easy to Navigate

Simple directional keypad

## Optimized

One-Touch Hot Keys  
Functionality

- Module/Breaker
- Code 39/Code 128
- Wire/Cable Flag
- Text Rotate/Text Align
- General & Fixed
- New & Exclusive:  
Custom Logic

## Familiar

NEW Computer-Style  
keyboard (QWERTY)

## Intuitive

Menu bar for access to  
symbol, term and label  
library and more

## Long Lasting

Li-Ion battery capable

## Print Key

Prints multiple  
copies

**Personalized**  
"Favorites" key

## Durable

Integrated rubber  
bumpers



## One-Touch Hot Keys




# 3M™ Portable Labeler PL200

A great portable labeling solution for high-end electrical, MRO, datacom and construction professionals is more than a tool. The 3M™ Portable Labeler PL200 is the advanced, easy-to-use labeling system that puts a premium on your reputation and time. Used in real-world jobsite conditions, the rugged, powerful and lightweight 3M Portable Labeler PL200 offers unique features and functionality to make your job easier. The PL200 accommodates 1/4", 3/8", 1/2" and 3/4" labels.



## One-Touch Hot Keys



# 3M™ Portable Labeler PL300

The new 3M™ Portable Labeler PL300 is a revolutionary printer with ideal ease-of-use, functionality, and advanced PC connectivity. The 3M PL300 printer features one-touch hot keys for quick and easy creation of commonly used label types. Utilizing the 3M Portable Labeler Software, the installer can create labels before reaching the worksite or create and edit labels on site. The PL300 accommodates 1/4", 3/8", 1/2", 3/4" and 1" labels.



## One-Touch Hot Keys



## 3M™ Portable Labeler Ordering Information

| Labeler Specifications             | Dimensions                                            | Unit Weight           | Power                                                                                                                                                                                                                                                                      |
|------------------------------------|-------------------------------------------------------|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| PL150                              | 7" x 4.6" x 2.25"<br>17.8 cm x 11.7 cm x 5.7 cm       | 2.0 lbs.<br>(.91kg)   | 6AA batteries (not included) or optional lithium ion batteries (not included)                                                                                                                                                                                              |
| PL150K                             | 10.83" x 10.43" x 3.62"<br>27.5 cm x 26.5 cm x 9.2 cm | 2.5 lbs.<br>(1.14 kg) | Lithium-ion rechargeable battery with AC adaptor (included) or 6AA batteries (not included)                                                                                                                                                                                |
| PL200                              | 9.2" x 4.9" x 2.5"<br>23.4 cm x 12.5 cm x 6.35 cm     | 2.0 lbs.<br>(.91kg)   | 6AA batteries (not included) or optional lithium ion batteries (not included)                                                                                                                                                                                              |
| PL200K                             | 13.75" x 14.5" x 4.7"<br>34.9 cm x 36.8 cm x 11.9 cm  | 5.5 lbs.<br>(2.49kg)  | Lithium-ion rechargeable battery with AC adaptor (included) or 6AA batteries (not included)                                                                                                                                                                                |
| PL300                              | 9.7" x 5.4" x 2.5"<br>24.6 cm x 13.7 cm x 6.4 cm      | 4.0 lbs.<br>(1.81kg)  | 6AA batteries (not included) or optional lithium ion rechargeable battery (not included)                                                                                                                                                                                   |
| PL300K                             | 13.75" x 17.5" x 4"<br>34.9 cm x 44.5 cm x 10.2 cm    | 5.0 lbs.<br>(2.27kg)  | Quick-charge lithium-ion rechargeable battery with AC adaptor (included) or 6AA batteries (not included)                                                                                                                                                                   |
| Labeler & Kit Description          | Product No.                                           | UPC<br>051128         | Includes                                                                                                                                                                                                                                                                   |
| 3M PL150 Single Unit               | PL150                                                 | 58374                 | 3M Portable Labeler PL150<br>1 User guide and quick reference guide<br>1 Refill cartridge 1/2" Black/White vinyl                                                                                                                                                           |
| 3M PL150 Soft Case Kit             | PL150K                                                | 60251                 | 3M Portable Labeler PL150<br>1 Quick Reference Guide<br>1 Refill Cartridge 1/2" Black/White Vinyl<br>3M Rechargeable Lithium-Ion Battery Pack PL150-PL200-BAT<br>3M AC Adaptor PL-ACPS                                                                                     |
| 3M PL200 Single Unit               | PL200                                                 | 58456                 | 3M Portable Labeler PL200<br>1 User guide on CD-ROM and quick reference guide<br>1 Refill cartridge 3/4" (19 mm) White vinyl                                                                                                                                               |
| 3M PL200 Hard Case Kit             | PL200K                                                | 58508                 | 3M Portable Labeler PL200<br>1 User guide on CD-ROM and quick reference guide<br>1 Refill cartridge 1/2" (12 mm) White polyester<br>1 Refill cartridge 3/4" (19 mm) White vinyl<br>3M Rechargeable lithium-ion battery pack PL150-PL200-BAT<br>3M AC adaptor PL-ACPS       |
| 3M PL300 Single Unit               | PL300                                                 | 59104                 | 3M Portable Labeler PL300<br>1 User guide on CD-ROM and quick reference guide<br>1 Refill cartridge 3/4" (19 mm) White vinyl                                                                                                                                               |
| 3M PL300 Hard Case Kit             | PL300K                                                | 58455                 | 3M Portable Labeler PL300 and software<br>1 User guide and quick reference guide<br>1 Refill cartridge 1/2" (12 mm) Black on white polyester<br>1 Refill cartridge 3/4" (19 mm) White vinyl<br>3M Rechargeable lithium-ion battery pack PL300-BAT<br>3M AC adaptor PL-ACPS |
| Accessory Description              | Product No.                                           | UPC<br>051128         | Compatibility                                                                                                                                                                                                                                                              |
| 3M PL150 Soft Case                 | PL150 Softcase                                        | 60252                 | PL150                                                                                                                                                                                                                                                                      |
| 3M PL150-PL200 Lithium Ion Battery | PL150-PL200-BAT                                       | 58517                 | PL150, PL200                                                                                                                                                                                                                                                               |
| 3M AC Adaptor                      | PL-ACPS                                               | 58518                 | PL150, PL200, PL300                                                                                                                                                                                                                                                        |
| 3M PL200 Hard Case                 | PL-HARDCASE                                           | 58515                 | PL200                                                                                                                                                                                                                                                                      |
| 3M PL300 Battery Pack              | PL300-BAT                                             | 58520                 | PL300                                                                                                                                                                                                                                                                      |
| 3M PL300 Hard Case                 | PL300-HARDCASE                                        | 59108                 | PL300                                                                                                                                                                                                                                                                      |

# Easy to Peel Labels That Stay Stuck

3M™ Portable Labeler Refill Cartridges are available in a choice of industrial-grade label materials for various surfaces and environments that resist UV, chemicals, water and oils. Labels are easy to load, print, and peel and are smear-, smudge-, and fade-resistant. Print labels meet OSHA, ANSI & ISO color standards. Engineered to stick on challenging surfaces. Labels are available in vinyl, nylon, polyester, heat shrink, non-adhesive and self-laminating in various sizes.

## High-Performance Label Options for the 3M™ Portable Labeler Family

|            |           | Vinyl                | Nylon          | Polyester                  | Heat Shrink                | Non-Adhesive | Self-Laminating (PL300 Only) |
|------------|-----------|----------------------|----------------|----------------------------|----------------------------|--------------|------------------------------|
| Labels     | Length    | 18.0'                | 11.5'          | 18.0'                      | 5.0'                       | 18.0'        | 18.0'                        |
|            | Width     | 3/8," 1/2," 3/4," 1" | 1/2," 3/4," 1" | 1/4," 3/8," 1/2," 3/4," 1" | 1/4," 3/8," 1/2," 3/4," 1" | 1/4," 1/2"   | 1"                           |
|            | Color     |                      |                |                            |                            |              |                              |
|            | Outdoor   | X                    |                |                            |                            |              |                              |
| Surfaces   | Flat      | X                    | X              | X                          |                            | X            |                              |
|            | Wiring    | X                    | X              |                            | X                          |              | X                            |
|            | Flag      | X                    | X              |                            |                            |              |                              |
|            | Textured  | X                    | X              | X                          |                            |              |                              |
| Resistance | UV        | X                    |                | X                          | X                          |              | X                            |
|            | Water     | X                    |                | X                          | X                          |              | X                            |
|            | Chemicals | X                    |                | X                          | X                          |              | X                            |
|            | Oils      | X                    |                | X                          | X                          |              | X                            |

## 3M™ Portable Labeler Refill Cartridges Ordering Information

| Product Number  | Description                                                   | UPC<br>051128 | Compatibility       | Color |
|-----------------|---------------------------------------------------------------|---------------|---------------------|-------|
| PLP-BLK-WHT-1/4 | Polyester Tape 1/4" (6 mm). Black Font. White Label.          | 59383         | PL150, PL200, PL300 | Black |
| PLP-WHT-3/8     | Polyester Tape 3/8" (9 mm). Black Font. White Label.          | 58485         | PL150, PL200, PL300 | Black |
| PLP-WHT-1/2     | Polyester Tape 1/2" (12 mm). Black Font. White Label.         | 58486         | PL150, PL200, PL300 | Black |
| PLP-WHT-3/4     | Polyester Tape 3/4" (19mm). Black Font. White Label.          | 58487         | PL150, PL200, PL300 | Black |
| PLP-WHT-1       | Polyester Tape 3/4" (24mm). Black Font. White Label.          | 58488         | PL300               | Black |
| PLP-BLK-CLR-1/4 | Polyester Tape 1/4" (6mm). Black Font. Clear Label.           | 59382         | PL150, PL200, PL300 | Black |
| PLP-CLR-3/8     | Polyester Tape 3/8" (9mm). Black Font. Clear Label.           | 58489         | PL150, PL200, PL300 | Black |
| PLP-CLR-1/2     | Polyester Tape 1/2" (12mm). Black Font. Clear Label.          | 58506         | PL150, PL200, PL300 | Black |
| PLP-CLR-3/4     | Polyester Tape 3/4" (19mm). Black Font. Clear Label.          | 58507         | PL150, PL200, PL300 | Black |
| PLP-BLK-CLR-1   | Polyester Tape 1" (24 mm). Black Font. Clear Label.           | 59386         | PL300               | Black |
| PLP-BLK-MTL-1/4 | Polyester Tape 1/4" (6 mm). Black Font. Metal Label.          | 59387         | PL150, PL200, PL300 | Black |
| PLP-MTL-3/8     | Polyester Tape 3/8" (9 mm). Black Font. Metal Label.          | 58492         | PL150, PL200, PL300 | Black |
| PLP-MTL-1/2     | Polyester Tape 1/2" (12 mm) Black Font. Metal Label.          | 58490         | PL150, PL200, PL300 | Black |
| PLP-MTL-3/4     | Polyester Tape 3/4" (19 mm). Black Font. Metal Label.         | 58491         | PL150, PL200, PL300 | Black |
| PLP-BLK-MTL-1   | Polyester Tape 1" (24 mm). Black Font. Metal Label.           | 59391         | PL300               | Black |
| PLHS-WHT-1/4    | Heat Shrinking Tubing 1/4" (6 mm). Black Font. White Label.   | 58483         | PL150, PL200, PL300 | Black |
| PLHS-WHT-3/8    | Heat Shrinking Tubing 3/8" (9 mm). Black Font. White Label.   | 58475         | PL150, PL200, PL300 | Black |
| PLHS-WHT-1/2    | Heat Shrinking Tubing 1/2" (12 mm). Black Font. White Label.  | 58476         | PL150, PL200, PL300 | Black |
| PLHS-WHT-3/4    | Heat Shrinking Tubing 3/4" (19 mm). Black Font. White Label.  | 58477         | PL150, PL200, PL300 | Black |
| PLHS-WHT-1      | Heat Shrinking Tubing 1" (24 mm). Black Font. White Label.    | 59375         | PL300               | Black |
| PLHS-YEL-1/4    | Heat Shrinking Tubing 1/4" (6 mm). Black Font. Yellow Label.  | 58484         | PL150, PL200, PL300 | Black |
| PLHS-YEL-3/8    | Heat Shrinking Tubing 3/8" (9 mm). Black Font. Yellow Label.  | 58478         | PL150, PL200, PL300 | Black |
| PLHS-YEL-1/2    | Heat Shrinking Tubing 1/2" (12 mm). Black Font. Yellow Label. | 58479         | PL150, PL200, PL300 | Black |
| PLHS-YEL-3/4    | Heat Shrinking Tubing 3/4" (19 mm). Black Font. Yellow Label. | 58480         | PL150, PL200, PL300 | Black |
| PLNA-WHT-1/4    | Non-Adhesive Tape 1/4" (6 mm). Black Font. White Label.       | 58493         | PL150, PL200, PL300 | Black |
| PLNA-WHT-1/2    | Non-Adhesive Tape 1/2" (12 mm). Black Font. White Label.      | 58495         | PL150, PL200, PL300 | Black |
| PLFN-WHT-1/2    | Flexible Nylon Tape 1/2" (12 mm). Black Font. White Label.    | 58509         | PL150, PL200, PL300 | Black |
| PLFN-WHT-3/4    | Flexible Nylon Tape 3/4" (19 mm). Black Font. White Label.    | 58510         | PL150, PL200, PL300 | Black |
| PLFN-WHT-1      | Flexible Nylon Tape 1" (24 mm). Black Font. White Label.      | 58511         | PL300               | Black |
| PLFN-YEL-1/2    | Flexible Nylon Tape 1/2" (12 mm). Black Font. Yellow Label.   | 58512         | PL150, PL200, PL300 | Black |
| PLFN-YEL-3/4    | Flexible Nylon Tape 1" (24 mm). Black Font. Yellow Label.     | 58513         | PL150, PL200, PL300 | Black |
| PLFN-YEL-1      | Flexible Nylon Tape 1" (24 mm). Black Font. Yellow Label.     | 58514         | PL300               | Black |

## 3M™ Portable Labeler Refill Cartridges Ordering Information

| Product Number  | Description                                               | UPC<br>051128 | Compatibility       | Color |
|-----------------|-----------------------------------------------------------|---------------|---------------------|-------|
| PLSL-WHT-1      | Self-Laminating Tape 1" (24 mm). Black Font. White Label. | 58583         | PL300               | Black |
| PLV-WHT-BLK-3/8 | Vinyl Tape 3/8" (9 mm). White Font. Black Label.          | 59378         | PL150, PL200, PL300 | White |
| PLV-WHT-BLK-1/2 | Vinyl Tape 1/2" (12 mm). White Font. Black Label.         | 59379         | PL150, PL200, PL300 | White |
| PLV-WHT-BLK-3/4 | Vinyl Tape 3/4" (19 mm). White Font. Black Label.         | 59380         | PL150, PL200, PL300 | White |
| PLV-WHT-BLK-1   | Vinyl Tape 1" (24 mm). White Font. Black Label.           | 59381         | PL300               | White |
| PLV-WHT-RED-1/2 | Vinyl Tape 1/2" (12 mm). White Font. Red Label.           | 59392         | PL150, PL200, PL300 | White |
| PLV-WHT-RED-3/4 | Vinyl Tape 3/4" (19 mm). White Font. Red Label.           | 59393         | PL150, PL200, PL300 | White |
| PLV-WHT-RED-1   | Vinyl Tape 1" (24 mm). White Font. Red Label.             | 59394         | PL300               | White |
| PLV-WHT-GRN-1/2 | Vinyl Tape 1/2" (12 mm). White Font. Green Label.         | 59401         | PL150, PL200, PL300 | White |
| PLV-WHT-GRN-3/4 | Vinyl Tape 3/4" (19 mm). White Font. Green Label.         | 59402         | PL150, PL200, PL300 | White |
| PLV-WHT-GRN-1   | Vinyl Tape 1" (24 mm). White Font. Green Label.           | 59403         | PL300               | White |
| PLV-WHT-BLU-1/2 | Vinyl Tape 1/2" (12 mm). White Font. Blue Label.          | 59404         | PL150, PL200, PL300 | White |
| PLV-WHT-BLU-3/4 | Vinyl Tape 3/4" (19 mm). White Font. Blue Label.          | 59405         | PL150, PL200, PL300 | White |
| PLV-WHT-BLU-1   | Vinyl Tape 1" (24 mm). White Font. Blue Label.            | 59406         | PL300               | White |
| PLV-WHT-PUR-1/2 | Vinyl Tape 1/2" (12 mm). White Font. Purple Label.        | 59407         | PL150, PL200, PL300 | White |
| PLV-WHT-PUR-3/4 | Vinyl Tape 3/4" (19 mm). White Font. Purple Label.        | 59408         | PL150, PL200, PL300 | White |
| PLV-WHT-PUR-1   | Vinyl Tape 1" (24 mm). White Font. Purple Label.          | 59409         | PL300               | White |
| PLV-WHT-BRN-1/2 | Vinyl Tape 1/2" (12 mm). White Font. Brown Label.         | 59410         | PL150, PL200, PL300 | White |
| PLV-WHT-BRN-3/4 | Vinyl Tape 3/4" (19 mm). White Font. Brown Label.         | 59411         | PL150, PL200, PL300 | White |
| PLV-WHT-BRN-1   | Vinyl Tape 1" (24 mm). White Font. Brown Label.           | 59412         | PL300               | White |
| PLV-BLK-GRY-1/2 | Vinyl Tape 1/2" (12 mm). Black Font. Gray Label.          | 59413         | PL150, PL200, PL300 | Black |
| PLV-BLK-GRY-3/4 | Vinyl Tape 3/4" (19 mm). Black Font. Gray Label.          | 59414         | PL150, PL200, PL300 | Black |
| PLV-BLK-GRY-1   | Vinyl Tape 1" (24 mm). Black Font. Gray Label.            | 59415         | PL300               | Black |
| PLV-WHT-3/8     | Vinyl Tape 3/8" (9 mm). Black Font. White Label.          | 58458         | PL150, PL200, PL300 | Black |
| PLV-WHT-1/2     | Vinyl Tape 1/2" (12 mm). Black Font. White Label.         | 58459         | PL150, PL200, PL300 | Black |
| PLV-WHT-3/4     | Vinyl Tape 3/4" (19 mm). Black Font. White Label.         | 58460         | PL150, PL200, PL300 | Black |
| PLV-BLK-WHT-1   | Vinyl Tape 1" (24 mm). Black Font. White Label.           | 59377         | PL300               | Black |
| PLV-YEL-1/2     | Vinyl Tape 1/2" (12 mm). Black Font. Yellow Label.        | 58462         | PL150, PL200, PL300 | Black |
| PLV-YEL-3/4     | Vinyl Tape 3/4" (19 mm). Black Font. Yellow Label.        | 58463         | PL150, PL200, PL300 | Black |
| PLV-BLK-YEL-1   | Vinyl Tape 1" (24 mm) Black Font. Yellow Label.           | 59400         | PL300               | Black |
| PLV-ORG-1/2     | Vinyl Tape 1/2" (12 mm). Black Font. Orange Label.        | 58468         | PL150, PL200, PL300 | Black |
| PLV-ORG-3/4     | Vinyl Tape 3/4" (19 mm). Black Font. Orange Label.        | 58469         | PL150, PL200, PL300 | Black |
| PLV-BLK-ORG-1   | Vinyl Tape 1" (24 mm). Black Font. Orange Label.          | 59397         | PL300               | Black |



# 3M™ Portable Labeler Embosser

## Metal tape embossing at your fingertips.

This portable metal tape embosser is tough enough to accompany you in the field and is easy to use. Since it can make labels on site that are capable of weathering the harshest conditions, there's no need for time-consuming trips to an engraving shop. All you'll have to do is type, cut and apply.

## 3M™ Portable Labeler Embossing Tape

| Product #    | Description                               | Length |
|--------------|-------------------------------------------|--------|
| PLE-ALNA-1/2 | Non-Adhesive Aluminum 1/2" (12 mm)        | 16'    |
| PLE-SSNA-1/2 | Non-Adhesive Stainless Steel 1/2" (12 mm) | 21'    |
| PLE-ALA-1/2  | Adhesive Aluminum 1/2" (12 mm)            | 12'    |



## 3M™ Portable Labeler Embossing Kit

- 1 3M™ Portable Labeler Embosser PLE – Metal Tape with Horizontal 0.188 inch (4,8 mm) Character Wheel
- 1 Reverse Image Wheel
- 1 Roll 1/2" (12 mm) x 16' (4,8 m) Non-Adhesive Aluminum Tape
- 1 Roll 1/2" (12 mm) x 21' (6,40 m) Non-Adhesive Stainless Steel Tape
- 1 Carrying Case
- 1 Instruction Manual





Ask about these additional solutions from 3M.



3M™ Wire  
Marking and ID

3M is a trademark of 3M Company. DYMO is a trademark of Newell Rubbermaid, LLC, Inc.

## Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

### **Portable Labeler Warranty; Limited Remedy; Limited Liability.**

This product will be free from defects in material and manufacturer for a period of twelve (12) months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or receive a refund for the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

### **Refill Cartridges Warranty; Limited Remedy; Limited Liability.**

This product will be free from defects in material and manufacture for a period of thirty (30) days from the time of purchase. If this product is defective, your exclusive remedy shall be, at 3M's option, to replace the 3M product or receive a refund for the purchase price. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



### **Electrical Markets Division**

6801 River Place Blvd.  
Austin, TX 78726-9000  
800 245 3573  
FAX 800 245 0329  
[www.3M.com/electrical](http://www.3M.com/electrical)

© 3M 2014. All rights reserved.  
80-6016-0706-4 (03410)TG-2