


SPOT - model: HR-1136

Low Voltage Miniature Recessed Downlights

WAC LIGHTING
Responsible Lighting®



Fixture Type:

Catalog Number:

Project: _____

Location: _____

PRODUCT DESCRIPTION

Low voltage miniature recessed bevel trim unit with clear glass lens. Used for lighting in cabinets, displays and similar wooden applications. Not intended for use in walls or ceilings.

FEATURES

- Shallow installation depth ideal for use in shelving, cabinets and displays.
- Not intended for use in walls or ceilings
- Mounts quickly with butterfly clips
- Requires a Class 2 transformer
- Lamp has a 35° adjustable tilt from nadir
- Order lamp separately
- The supplied clear glass lens can be replaced with one lens accessory.
- An all-in-one style recessed unit, comes with housing and trim - ready to install out of one box.
- Non-IC unit. Intended for installations where insulating materials will not be present.

SPECIFICATIONS

Materials: Housing is steel, painted black. Electrical components within the can are a bi-pin ceramic socket with nickel plating and 18 gauge teflon insulated wires with fiberglass sleeves. A total of 36" of insulated wires lead from the socket out the top of the can to the strip-prepared ends.

Transformers: Remote Class 2 Transformer required (order separately).

Light Source: Use one MR11 20W max, 12V lamp (order separately).

Mounting: 2 3/8" cutout hole. Two flat "wing" springs expand against the cut out hole to hold fixture against the surface. The insulated wires and socket are pre-installed in the housing with the wires leading out through the top of the housing. Simply connect to the remote class II transformer.

Standards: UL & CUL Listed

ORDER NUMBER

Model #	Finish
HR-1136	BK Black
	BN Brushed Nickel
	CB Copper Bronze
	CH Chrome
	WT White

HR-1136 -

Example: HR-1136-BK

CLASS 2 ENCLOSED ELECTRONIC TRANSFORMERS

Model	Input	Output	Dimensions
EN-1260-RB2	120V	12V, 1 × 60W	6 1/2" x 1 5/8" x 1 1/4"
EN-12120-RB2*		12V, 2 × 60W	6" x 3 1/4" x 2 5/8"
EN-12180-RB2*		12V, 3 × 60W	6 3/4" x 3 5/8" x 2 5/8"
EN-12300-RB2*		12V, 5 × 60W	8 1/2" x 4 5/8" x 2 5/8"

*Includes LED indicator lights and integral push in terminals

UL LISTED CLASS 2 PLUG-IN ELECTRONIC TRANSFORMERS

EN-1260-P-AR	120V	12V, 60W	2 3/4" x 1 5/8" x 1 3/4"	BK Black
				WT White

FINISHES



WAC Lighting
www.waclighting.com
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center
615 South Street • Garden City, NY 11530
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center
168 Brea Canyon Road • City of Industry, CA 91789
Phone (800) 526.2588 • Fax (800) 526.2585