

# Modular Metering Mini Mod III

Accessories  
Field Installed

## Section 2

### Accessories - Field Installed

Description	Product Number
Semi-Flush Kits	
-125A Sockets -2 gang	TMM12SF2
-3 and 4 gang	TMM12SF4
-5 and 6 gang	TMM12SF6
-2 gang	TMM20SF2
-200A Sockets -3 and 4 gang	TMM20SF4
-5 and 6 gang	TMM20SF6
Compression Lug Landing Kit -600 amp Includes 3 pads each with 2 threaded stud connections (and hardware) for compression or mechanical lugs with NEMA 2-hole bolt configuration (lugs not furnished). Not suitable for 2-gang	TMM6CLL
By-pass Kits	
Manual Slider-Type (Ring Type Only) <sup>1</sup>	
-125 amp top socket for 2, 3, 5 and 6 gang	TMBPM12TA
-125 amp for all other sockets	TMBPM12A
-200 amp for all sockets	TMBPM20A <sup>2</sup>
Jumper Straps Type <sup>1</sup> (use with TMCA)	TMBPJ20 <sup>4</sup>
Cover Including Jumper Strap Type-fits all (Ring Type Only) <sup>3</sup>	TMBPC20 <sup>4</sup>
Horn-Type-fits all (Ringless Only) <sup>1</sup>	TMBPH20A
Fifth Jaw Kits	
-Bused; 3, 6, or 9 o'clock mounting:	TMSJA
Order two for fifth and sixth jaw. Not suitable for 2-gang ring type	
-Isolated; 3 or 9 o'clock mounting	TMSJUA
Sealing Rings	
-Screw-Type, Aluminum	TSR1
-Snap Type, Stainless Steel	TSR3
-Screw and Lock-Type, Aluminum	TSR4
-Snap-Type, Aluminum (Standard)	TSR5
Steel Meter Socket Covers	
Blank (fits bottom position only)	
-125 Amp	TMCB12B
-200 Amp	TMCB12B
Ringless (Field -converts ring-type to ringless)	
-125 amp top socket for 2, 3, 5 and 6 gang	TMCR12T
-125 amp for all other sockets	TMCR12
-200 amp for all sockets	TMCR20
Lexan Meter socket Cover Plate (without tabs)	TMCA
Lexan Meter Socket Cover Plate	TMCP
Equipment Ground Bar, (6) 6-2/0	TMEG
Individual Meter Socket Barrier Kit (includes 6)	TMBR
Mounting Z-Rail, 4-foot	TMZR
Lug Kit for (3) 4/0 cable	TMPAL40

<sup>1</sup>100 amps continuous.

<sup>2</sup>For top socket on TMM4220R, order TMBPM20TA.

<sup>3</sup>200 amps continuous.

<sup>4</sup>Not UL Listed.



# Modular Metering Meter Mod III

Meter Stack Modules  
Single-Phase  
Plus Accessories

## Section 2

### Accessories — Field Installed

Type	Description	Product Number
By-pass Kit	Jumper Strap Type	TMBPJ20 <sup>1,3</sup>
By-pass Kit	Cover including Jumper Strap Type	TMBPC20 <sup>1</sup>
By-pass Kit	Horn Type	TMBPH20A <sup>3</sup>
By-pass Kit	Manual Slider Type	TMBPM12TA <sup>2</sup>
By-pass Kit	Manual Slider Type	TMBPM12A <sup>2</sup>
By-pass Kit	Manual Slider Type	TMBPM20A <sup>2</sup>
By-pass Kit	Jumper Strap Type	TMBPJ20
Fifth Jaw Kit, Bused		TM5JA
Fifth Jaw Kit, Isolated		TM5JUA
Sealing Ring, Screw Type, SS		TSR1
Sealing Ring, Snap Type, SS		TSR3
Sealing Ring, Screw & Lock Type, AL		TSR4
Sealing Ring, Snap Type, AL		TSR5
Meter Socket Cover, 125A		TMCB12B
Meter Socket Cover, 200A		TMCB20B
Meter Socket Cover, Ringless	125A	TMCR12T
Meter Socket Cover, Ringless	125A	TMCR12
Meter Socket Cover, Ringless	200A	TMCR20
Meter Socket Cover Plate without Tabs		TMCA
Meter Socket Cover Plate		TMCP
Equipment Ground Bar		TMEG
Individual Meter Socket Barrier Kit (Includes 6)		TMBR
Mounting Z Rail		TMZR
Spacer	4-inch, 4 cross bus rated 1200A	TMPS12
Elbow	16 inch x 16 inch, 4 cross bus rated 1200A	TMPE12 <sup>4</sup>
Elbow	12 inch x 12 inch, 4 cross bus rated 1200A	TMPE12A <sup>4</sup>
Main Module Door Closure Kit	Barrier Kit, Bottom Feed Main	TMP3FBB
Anti-Inversion Clip		TMIC
Endwall		TM234BEW200
Endwall		TM56BEW200

### Replacement Rating Plugs

Main Breaker Amperage	Rating Plug Amperage	Product Number
1600A	800A	TMP16RP08T
1600A	1000A	TMP16RP10T
1600A	1200A	TMP16RP12T
1600A	1250A	TMP16RP125T
1600A	1400A	TMP16RP14T
1600A	1500A	TMP16RP15T
1600A	1600A	TMP16RP16T
2000A	1000A	TMP20RP10T
2000A	1200A	TMP20RP12T
2000A	1250A	TMP20RP125T
2000A	1400A	TMP20RP14T
2000A	1600A	TMP20RP16T
2000A	2000A	TMP20RP20T

<sup>1</sup>Not UL listed.


<sup>2</sup>200 amps continuous.

<sup>3</sup>100 amps continuous.

<sup>4</sup>Indoor Type 1.



TMBPJ20



TMBPM12TA




TSR1



TSR3



TMCB12B




TMCR12



TMCR12T



TMCP



TMBR



TMZR



# Modular Metering Meter Mod III

Meter Stack Modules  
Single-Phase  
Plus Accessories

### Product Features

- Single-Phase/Three-Wire, 120/240 Vac or Three-Phase, Four-Wire, Horizontal Bus, 208Y/120 Vac System Voltage
- UL listed
- 1200 amp, 4-wire cross bus (aluminum)
- Front Accessible Field Phase Balancing by Meter Socket
- (1) 14-2 Equipment Ground per Socket, Factory Installed
- Only 225A and 400 Ringless Type meter stacks, contain lever bypass. 125A and 200A meter sockets do not contain lever bypass

### Ringless Type Socket w/ Lever Bypass

Socket Amps	No. of Sockets	Product Number
225A	1	TMPR12122R <sup>1</sup>
225A	2	TMPR12222R <sup>1</sup>
225A	3	TMPR12322R <sup>1</sup>
225A	4	TMPR12422R <sup>1</sup>
400A	1	TMPR12140RB <sup>1,2,10</sup>
400A	2	TMPR12240RB <sup>1,3,10</sup>
400A	1	TMPK12140RB <sup>1</sup>
400A	1	TMPK12140RBA <sup>1</sup>

### Ring Type Socket

Socket Amps	No. of Sockets	Product Number
225A	1	TMP8120RTAB <sup>4,5</sup>
225A	1	TMP8120RTBC <sup>4,5</sup>
225A	1	TMP8120RTAC <sup>4,5</sup>
225A	2	TMP112220RTAB <sup>4,5</sup>
225A	2	TMP112220RTAC <sup>4,5</sup>
225A	2	TMP112220RTBC <sup>4,5</sup>
225A	3	TMP112320RTAB <sup>4,5</sup>
225A	3	TMP112320RTAC <sup>4,5</sup>
225A	3	TMP112320RTBC <sup>4,5</sup>

One snap-type, aluminum sealing ring (TSR5) per socket included.

### Tenant Main Circuit Breakers 10,000 AIC

Socket Amps	Ampere Rating	Product Number
225	15	TEB122015 <sup>6</sup>
225	20	TEB122020 <sup>6</sup>
225	25	TEB122025 <sup>6</sup>
225	39	TEB122039 <sup>6</sup>
225	35	TEB122035 <sup>6</sup>
225	40	TEB122040 <sup>6</sup>
225	45	TEB122045 <sup>6</sup>
225	50	TEB122050 <sup>6</sup>
225	60	TEB122060 <sup>6</sup>
225	70	TEB122070 <sup>6</sup>
225	80	TEB122080 <sup>6</sup>
225	90	TEB122090 <sup>6</sup>
225	100	TQD22100
225	125	TQD22125
225	150	TQD22150
225	175	TQD22175
225	200	TQD22200
225	225	Use TMQD

### Tenant Main Circuit Breakers 22,000 AIC

Socket Amps	Ampere Rating	Product Number
200	100	THQD22100
200	125	THQD22125
200	150	THQD22150
200	175	THQD22175
200	200	THQD22200
200	225	Use TMQD



TMPR12122R

### Tenant Main Circuit Breakers 100,000 AIC

Socket Amps	Ampere Rating	Product Number
200	60	TMQD22060
200	70	TMQD22070
200	80	TMQD22080
200	90	TMQD22090
200	100	TMQD22100
200	125	TMQD22125
200	150	TMQD22150
200	175	TMQD22175
200	200	TMQD22200
200	225	TMQD22225

### Accessories — Field Installed

Type	Description	Product Number
TEB Breaker		TMTEB
Mounting Kit		
Barrel Lock Bracket and Guard Kit		TMBL7
Bypass Kit	Totalizing Jumper Type	TMBPT320 <sup>7,8</sup>
Blank Meter		
Socket Cover	Fits all positions	TMCB322A
Individual Meter		TMBR3
Socket Barrier Kit (Includes 6)		
Insulator for Lever		TMHN
By-pass Handle		
Mounting Z Rail	4-foot	TMZR
Spacer	4 inch,	TMPS12
	4 cross bus rated, 1200A	
Elbow	16 inch x 16 inch,	TMPE12 <sup>9</sup>
	4 cross bus rated 1200A	
Elbow	12 inch x 12 inch,	TMPE12A <sup>9</sup>
	4 cross bus rated 1200A	

<sup>1</sup>Only 225A and 400A are lever bypass.

<sup>2</sup>One 400A tenant breaker included.

<sup>3</sup>Two 400A tenant breakers included.

<sup>4</sup>Meets EUSERC requirements. T- suffix signifies test bypass kit. Suffixes AB, BC, AC reflect the factory-set phase balancing.

<sup>5</sup>Included factory-installed fifth jaw (TM5JA Bused).

<sup>6</sup>Requires one TMTEB per breaker.

<sup>7</sup>Not UL listed.

<sup>8</sup>180 amps continuous.

<sup>9</sup>Indoor, Type 1.

<sup>10</sup>See Page 2-8 for alternate 400A Rating Plugs

