


















# Jumbo/Oversize

	NOTE: X following Catalog Number denotes that straps are not supplied.	STAIN-LESS TYPE 302	SATIN BRASS (.040")	ALUMI-NUM (.050")	STAIN-LESS TYPE 430	BROWN WRINKLE	IVORY WRINKLE
	30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole (3D-SL)	93847	94847	95847	97847	98847	99847
	30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole 2 Gang Plate (23D-SL)	93937	94937	95937	97937	98937	99937
	Block Duplex/GFI Recept. (SRM-SL)	93834	94834	95834	97834	98834	99834
	2 Block Duplex/GFI Recepts. (2SRM-SL)	93835	94835	95835	97835	98835	99835
	Interchangeable 1 Hole Horizontal (71A-SL)	93911X	94911X	95911X	97911X	98911X	99911X
	Interchangeable 2 Holes (71B-SL)	93921X	94921X	95921X	97921X	98921X	99921X
	Interchangeable 3 Holes (71C-SL)	93931X	94931X	95931X	97931X	98931X	99931X
	Toggle Switch, Duplex Recept. (1T-10DR-SL)	93832	94832	95832	97832	98832	99832
	Toggle Switch, Block Duplex/GFI Recept. (1T-SRM-SL)	93865	94865	95865	97865	98865	99865
	Duplex Recept., Single Recept. (1.405" ID Hole) (10DR-10R-SL)	93842	94842	95842	97842	98842	99842
	Toggle Switch, Centered 2 Gang Plate (1T-2G-SL)	93971	94971	95971	97971	98971	99971
	Duplex Recept., Centered 2 Gang Plate (10DR-2G-SL)	93901	94901	95901	97901	98901	99901
	Single Recept., Centered 2 Gang Plate (1.405" ID Hole) (10R-2G-SL)	93991	94991	95991	97991	98991	99991
	2 Toggle Switches, Duplex Receptacle (2T-10DR-SL)	93843	94843	95843	97843	98843	99843
	2 Toggle Switches, Block Duplex/GFI Recept. (2T-SRM-SL)	93883	94883	95883	97883	98883	99883
	Toggle Switch, 2 Duplex Recepts. (1T-20DR-SL)	93863	94863	95863	97863	98863	99863
	3 Toggle Switches, Duplex Recept. (3T-10DR-SL)	93844	94844	95844	97844	98844	99844

# Material Specifications

Stainless Steel	Type 302 Spec. Grade (18% chrome-8% nickel) Non-Magnetic and Corrosion Resistant For hospitals, schools and other public institutions.	Finish	Shape	Thickness	U.S. Bureau Standards Symbols	Finish Designator	Cat. Page #
	(302SS)	#4 Fine Satin	S	.035	US #32D	93000	A7-13
	(302SS-PRL)	#4 Fine Satin	P	.035	US #32D	53000	A42-47
	(302-6SS)	#4 Fine Satin	S	.060	US #32D	70000	A28-34
	(302SP)	Mirror Polish	S	.035	US #32	68000	A28-34
	Type 430 (SS)	#4 Fine Satin	S	.030	US #32	97000	A7-13
Type 430 (SS-PRL)	#4 Fine Satin	P	.030	US #32D	57000	A42-47	

Aluminum	Clear Anodized (5AA)	Matte, Smooth	S	.050	US #28	95000	A28-34
	Clear Anodized (5AA-PRL)	Matte, Smooth	P	.050	US #28	55000	A42-47
	Bright Satin (SAL)	Satin	S	.040	—	62000	A28-34

Brass & Bronze Lacquered to prevent oxidation	Statuary Bronze Dark (4DBR)	Antiqued, Relieved	S	.040	US #20	69000	A35-41
	Bank Bronze Medium (4ABR)	Antiqued, Relieved	S	.040	US #10B	65000	A35-41
	Satin Brass (4BB)	Satin #4 Polish	S	.040	US #4	94000	A28-34
	Satin Brass (4BB-PRL)	Satin #4 Polish	P	.040	US#4	54000	A42-47
	Satin Brass (6BB)	Satin #4 Polish	S	.060	US #4	96000	A28-34
	Satin Bronze (4SBR)	Satin #4 Polish	S	.040	US #10	66000	A35-41
	Satin Bronze (4SBR-PRL)	Satin #4 Polish	P	.040	US #10	56000	A42-47
	Polished Brass (4PB)	Mirror Finish	S	.040	US #3	64000	A28-34

Lexan® Thermoplastic	Brown	91000	A54-57
	Gray	77000G	A54-57
	Ivory	92000	A54-57
	Red	77000R	A54-57
	White	90000	A54-57

# CATALOG SECTION A

---



## WALL PLATES

- Standard • Princess • Oversize • Narrow
- Endura/Lexan • Maxi • Deep • Data Transmission
- Emergency • Accessories

---

*Mulberry*