

Reliable performance

Core & Coil (71A) MH 175W - 450W

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Benefits

- Vacuum-pressure impregnation is used to re-enforce the electrical insulation of the ballast, preclude moisture, inhibit noise, and dissipate heat
- Pre-insulated voltage leads reduce the risk of shock and shrink installation time

Features


- Vacuum-pressure impregnated with a silica-filled polyester varnish
- All core and coil ballasts below 600W utilize a UL Class H (180°C) insulation system
- C and C ballasts 600W and higher utilize a UL Class N (200°C) insulation system
- Pre-insulated voltage leads
- Ballast kits supplied with pre-wired ignitor

Application

- High bay retail, manufacturing, gymnasiums, warehouses, parking structures, outdoor


Core & Coil (71A) MH 175W - 450W

Versions



Core & Coil (71A) MH 175W - 450W

Dimensional drawing



Product	A1	B1	C1	A2		
CORE & COIL HID	165.1	88.9	111.76	146.05		
71A5790500DMLA	mm	mm	mm	mm		
CORE & COIL HID	3.15 in	1.65 in	4.8 in	4.4 in	4.3 in	3.9 in
71A57H0500DMLA						
CORE & COIL HID	4.10 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in
71A6092600AEE						
CORE & COIL HID	4.41 in	3.20 in	3.9 in	3.5 in	2.8 in	2.4 in
71A5593500DEE						
CORE & COIL HID	3.8 in	2.04 in	4.8 in	4.4 in	4.3 in	3.9 in
71A60N2500D						
CORE & COIL HID	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
71A5742520DTEE						
CORE & COIL HID	3.90 in	2.10 in	4.8 in	4.4 in	4.3 in	3.9 in
71A6042600TAAE						
CORE & COIL HID 71A60N1500	3.7 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5741001D	4.2 in	3 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID	3.10 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
71A5792500DMLA						
CORE & COIL HID	3.90 in	2.25 in	4.8 in	4.4 in	4.3 in	3.9 in
71A6393500DEE						
CORE & COIL HID	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
71A5742510DTEE						
CORE & COIL HID 71A5590500D	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID	3.25 in	1.75 in	4.8 in	4.4 in	4.3 in	3.9 in
71A57N2500D						
CORE & COIL HID	3.77 in	2.06 in	4.8 in	4.4 in	4.3 in	3.9 in
71A5892510DAEE						
CORE & COIL HID	4.20 in	2.95 in				
71A5692520DEE						
CORE & COIL HID 71A57A2500D	3.1 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID	3.5 in	2.24 in	3.9 in	3.5 in	2.8 in	2.4 in
71A5593500DML						
CORE & COIL HID 71A6092001D	4.1 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID	4 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
71A5752500DAEE						
CORE & COIL HID	4.00 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
71A60A1500DA						
CORE & COIL HID	3.7 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
71A5541500DTEE						
CORE & COIL HID	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
71A5590500DML						
CORE & COIL HID 71A61E6500D	3.8 in	2.2 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5540001D	4 in	2.4 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A57A0001D	3.1 in	1.64 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID	3.55 in	1.61 in	4.8 in	4.4 in	4.3 in	3.9 in
71A5792500DEE						
CORE & COIL HID	4.30 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
71A6052500DAEE						
CORE & COIL HID	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
71A6091500DA						

Core & Coil (71A) MH 175W - 450W

Dimensional drawing

Product	A1	B1	C1	A2		
CORE & COIL HID 71A6091500DMLA	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A57A0600A	3.10 in	1.64 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6042510DTAEE	3.90 in	2.10 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6092500DMLA	4.10 in	2.10 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6041500D	4 in	2 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6052600AEE	4.30 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6042001D	3.9 in	2.11 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5943500DTAEE	4.15 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5790500DA	3.15 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5590510D	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5792510DEE	3.55 in	1.61 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6092510DAEE	4.10 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5892500DMLA	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55A0500D	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A55A0001D	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A60E6500	4 in	2.4 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55A0600	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5543500DTEE	4.20 in	3.10 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A60A2500DA	3.80 in	1.97 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5892001D	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A1600A	4 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792520DEE	3.55 in	1.61 in				
CORE & COIL HID 71A5943600TAEE	4.15 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5593001D	3.5 in	2.24 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5593600EE	4.41 in	3.20 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5752001D	4 in	2.2 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792600EE	3.55 in	1.61 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5842001DT	3.65 in	1.77 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5750001D	3.1 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5842500DTAEE	4.10 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792001D	3.1 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID AS205WQUAD500DEE	3.68 in	1.71 in	4.8 in	4.4 in	4.3 in	3.9 in

Core & Coil (71A) MH 175W - 450W

Product	A1	B1	C1	A2		
CORE & COIL HID 71A5993500DAEE	4.05 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A58A2500DA	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5852500DAEE	4.11 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5692500DEE	4.20 in	2.95 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6092500DAEE	4.10 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5543600TEE	4.20 in	3.10 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5993600AEE	4.05 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5770001D	3.15 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5993001D	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5771001D	4.2 in	3 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5791500D	4.2 in	3 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5591500DEE	3.30 in	1.65 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A56A2500D	3.6 in	2.45 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A57A0500D	3.1 in	1.64 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A57N0500D	3.4 in	1.78 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5692001D	3.6 in	2.45 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A58N2510D	3.8 in	2.05 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6051001D	4.45 in	2.34 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5692510DEE	4.20 in	2.95 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5742500DTEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A59A3500DA	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5892600AEE	3.77 in	2.06 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792500DXEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55A0610	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A60H1500DMLA	4.05 in	2.14 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A2600A	3.80 in	1.97 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5742600TEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6041001D	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5570001D	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6052001D	4.3 in	2.2 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6091510DA	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6071001D	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55A3500D	3.5 in	2.24 in	3.9 in	3.5 in	2.8 in	2.4 in

Core & Coil (71A) MH 175W - 450W

Product	A1	B1	C1	A2		
CORE & COIL HID 71A6343500DTEE	4.15 in	2.40 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5993510DAEE	4.05 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A2510DA	3.8 in	1.97 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A1001D	4 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55H0500DML	3.87 in	2.4 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A58N2500D	3.8 in	2.05 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5842510DTAEE	4.10 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID AS205W480T500DEE	3.68 in	1.71 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5892500DAEE	3.77 in	2.06 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5593510DEE	4.41 in	3.20 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5642500DTEE	4.15 in	2.90 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6041500DMLA	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55N0500	4 in	2.75 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5953500DAEE	4.10 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in

General Information

Number Of Lamps	1
-----------------	---

Operating and Electrical

order code	Input Frequency	Input Voltage
71A55N0500	50	120/220-240
71A57N0500D	50	120/220-240
71A57A2500D	60	120/277/347
71A55A3500D	60	120/277/347
71A5593001D	60	120/208/240/277
71A55A0500D	60	120/277/347
71A55A0600	60	120/277/347
71A55A0610	60	120/277/347
71A5741001D	60	480
71A6041500D	60	480
71A60A1500DA	60	120/277/347
71A60A2510DA	60	120/277/347
71A57A0500D	60	120/277/347
71A5791500D	60	120/208/240/277
71A55A0001D	60	120/277/347
71A57A0001D	60	120/277/347
71A6071001D	60	120/208/240/277
71A60A1001D	60	120/277/347

order code	Input Frequency	Input Voltage
71A5570001D	60	120/208/240/277
71A5692001D	60	120/208/240/277
71A56A2500D	60	120/277/347
71A5770001D	60	120/208/240/277
71A5771001D	60	120/208/240/277
71A5892001D	60	120/208/240/277
71A5993001D	60	120/208/240/277
71A6041001D	60	480/120T
71A6092001D	60	120/208/240/277
71A60E6500	60	120/208/240
71A61E6500D	60	120/208/240
71A5540001D	60	480
71A60N1500	50	120/220-240
71A5590500D	60	120/208/240/277
71A5541500DTEE	60	480/120T
71A55H0500DML	60	127/220
71A57H0500DMLA	60	127/220
71A60H1500DMLA	60	127/220

Core & Coil (71A) MH 175W - 450W

order code	Input Frequency	Input Voltage
71A6052001D	60	120/208/240/277/480
71A5792500DXEE	60	120/208/240/277
AS205W480T500DEE	60	480
AS205WQUAD500DEE	60	120/208/240/277
71A5752001D	60	120/208/240/277/480
71A6042001D	60	480/120T
71A5750001D	60	120/208/240/277/480
71A5792001D	60	120/208/240/277
71A6051001D	60	120/208/240/277/480
71A57N2500D	50	120/220-240
71A58N2500D	50	120/220-240
71A60N2500D	50	120/220-240
71A5590510D	60	120/208/240/277
71A58N2510D	50	120/220-240
71A6091510DA	60	120/208/240/277
71A5590500DML	60	120/208/240/277
71A5593500DML	60	120/208/240/277
71A5790500DA	60	120/208/240/277
71A5892500DMLA	60	120/208/240/277
71A6091500DA	60	120/208/240/277
71A6091500DMLA	60	120/208/240/277
71A58A2500DA	60	120/277/347
71A59A3500DA	60	120/277/347
71A60A2500DA	60	120/277/347
71A60A1600A	60	120/277/347
71A5842001DT	60	480/120T
71A60A2600A	60	120/277/347
71A5792500DMLA	60	120/208/240/277
71A57A0600A	60	120/277/347
71A6041500DMLA	60	480
71A6092500DMLA	60	120/208/240/277
71A5790500DMLA	60	120/208/240/277
71A5593500DEE	60	120/208/240/277
71A5591500DEE	60	120/208/240/277
71A5543500DTEE	60	480/120T
71A5692500DEE	60	120/208/240/277

order code	Input Frequency	Input Voltage
71A5642500DTEE	60	480/120T
71A5742500DTEE	60	480/120T
71A5792500DEE	60	120/208/240/277
71A5842500DTAEE	60	480/120T
71A5892500DAEE	60	120/208/240/277
71A5943500DTAEE	60	480/120T
71A5993500DAEE	60	120/208/240/277
71A5892510DAEE	60	120/208/240/277
71A5892600AEE	60	120/208/240/277
71A5842510DTAEE	60	480/120T
71A5993510DAEE	60	120/208/240/277
71A5993600AEE	60	120/208/240/277
71A5943600TAEE	60	480/120T
71A6092500DAEE	60	120/208/240/277
71A6092510DAEE	60	120/208/240/277
71A6092600AEE	60	120/208/240/277
71A6042510DTAEE	60	480/120T
71A6042600TAEE	60	480/120T
71A5593600EE	60	120/208/240/277
71A5692510DEE	60	120/208/240/277
71A5742510DTEE	60	480/120T
71A5792510DEE	60	120/208/240/277
71A5792600EE	60	120/208/240/277
71A5543600TEE	60	480/120T
71A5593510DEE	60	120/208/240/277
71A6052500DAEE	60	120/240/208/277/480
71A5792520DEE	60	120/208/240/277
71A5742520DTEE	60	480/120T
71A5852500DAEE	60	120/208/240/277/480
71A5953500DAEE	60	120/208/240/277/480
71A5752500DAEE	60	120/208/240/277/480
71A5692520DEE	60	120/208/240/277
71A5742600TEE	60	480/120T
71A6393500DEE	60	120/208/240/277
71A6052600AEE	60	120/240/208/277/480
71A6343500DTEE	60	480/120T

General Information

order code	Capacitor Value	Lamp Type
71A55N0500	12 MFD	175/150W MH
71A57N0500D	18 MFD	250W MH
71A57A2500D	17 MFD	250W MH
71A55A3500D	11 MFD	175W MH
71A5593001D	11 MFD	175W MH
71A55A0500D	10 MFD	175/150W MH
71A55A0600	10 MFD	175/150W MH
71A55A0610	10 MFD	175/150W MH
71A5741001D	15 MFD	250W MH
71A6041500D	24 MFD	400W MH
71A60A1500DA	24 MFD	400W MH
71A60A2510DA	26 MFD	400W MH

order code	Capacitor Value	Lamp Type
71A57A0500D	15 MFD	250W MH
71A5791500D	15 MFD	250W MH
71A55A0001D	10 MFD	175/150W MH
71A57A0001D	15 MFD	250W MH
71A6071001D	24 MFD	400W MH
71A60A1001D	24 MFD	400W MH
71A5570001D	10 MFD	175/150W MH
71A5692001D	15 MFD	200W MH
71A56A2500D	15 MFD	200W MH
71A5770001D	15 MFD	250W MH
71A5771001D	15 MFD	250W MH
71A5892001D	21 MFD	320W MH

Core & Coil (71A) MH 175W - 450W

order code	Capacitor Value	Lamp Type
71A5993001D	22.5 MFD	350W MH
71A6041001D	24 MFD	400W MH
71A6092001D	26 MFD	400W MH
71A60E6500	20 MFD	400W MH
71A61E6500D	26 MFD	400W MH
71A5540001D	10 MFD	175/150W MH
71A60N1500	24 MFD	400W MH
71A5590500D	10 MFD	175/150W MH
71A5541500DTEE	11 MFD	175W MH
71A55H0500DML	10 MFD	175/150W MH
71A57H0500DMLA	15 MFD	250W MH
71A60H1500DMLA	24 MFD	400W MH
71A6052001D	26 MFD	400W MH
71A5792500DXEE	17 MFD	250W MH
AS205W480T500DEE	16 MFD	205W MH
AS205WQUAD500DEE	16 MFD	205W MH
71A5752001D	17 MFD	250W MH
71A6042001D	26 MFD	400W MH
71A5750001D	15 MFD	250W MH
71A5792001D	17 MFD	250W MH
71A6051001D	24 MFD	400W MH
71A57N2500D	20 MFD	250W MH
71A58N2500D	24 MFD	320W MH
71A60N2500D	30 MFD	400W MH
71A5590510D	10 MFD	175/150W MH
71A58N2510D	24 MFD	320W MH
71A6091510DA	24 MFD	400W MH
71A5590500DML	10 MFD	175/150W MH
71A5593500DML	11 MFD	175W MH
71A5790500DA	15 MFD	250W MH
71A5892500DMLA	21 MFD	320W MH
71A6091500DA	24 MFD	400W MH
71A6091500DMLA	24 MFD	400W MH
71A58A2500DA	21 MFD	320W MH
71A59A3500DA	22.5 MFD	350W MH
71A60A2500DA	26 MFD	400W MH
71A60A1600A	24 MFD	400W MH
71A5842001DT	21 MFD	320W MH
71A60A2600A	26 MFD	400W MH
71A5792500DMLA	17 MFD	250W MH
71A57A0600A	15 MFD	250W MH
71A6041500DMLA	24 MFD	400W MH

order code	Capacitor Value	Lamp Type
71A6092500DMLA	26 MFD	400W MH
71A5790500DMLA	15 MFD	250W MH
71A5593500DEE	11 MFD	175W MH
71A5591500DEE	11 MFD	175W MH
71A5543500DTEE	11 MFD	175W MH
71A5692500DEE	15 MFD	200W MH
71A5642500DTEE	15 MFD	200W MH
71A5742500DTEE	17 MFD	250W MH
71A5792500DEE	17 MFD	250W MH
71A5842500DTAEE	21 MFD	320W MH
71A5892500DAEE	21 MFD	320W MH
71A5943500DTAEE	22.5 MFD	350W MH
71A5993500DAEE	22.5 MFD	350W MH
71A5892510DAEE	21 MFD	320W MH
71A5892600AEE	21 MFD	320W MH
71A5842510DTAEE	21 MFD	320W MH
71A5993510DAEE	22.5 MFD	350W MH
71A5993600AEE	22.5 MFD	350W MH
71A5943600TAEE	22.5 MFD	350W MH
71A6092500DAEE	26 MFD	400W MH
71A6092510DAEE	26 MFD	400W MH
71A6092600AEE	26 MFD	400W MH
71A6042510DTAEE	26 MFD	400W MH
71A6042600TAEE	26 MFD	400W MH
71A5593600EE	11 MFD	175W MH
71A5692510DEE	15 MFD	200W MH
71A5742510DTEE	17 MFD	250W MH
71A5792510DEE	17 MFD	250W MH
71A5792600EE	17 MFD	250W MH
71A5543600TEE	11 MFD	175W MH
71A5593510DEE	11 MFD	175W MH
71A6052500DAEE	26 MFD	400W MH
71A5792520DEE	17 MFD	250W MH
71A5742520DTEE	17 MFD	250W MH
71A5852500DAEE	21 MFD	320W MH
71A5953500DAEE	22.5 MFD	350W MH
71A5752500DAEE	17 MFD	250W MH
71A5692520DEE	15 MFD	200W MH
71A5742600TEE	17 MFD	250W MH
71A6393500DEE	26.5 MFD	450W MH
71A6052600AEE	26 MFD	400W MH
71A6343500DTEE	26.5 MFD	450W MH

Mechanical and Housing

order code	Housing
71A55N0500	-
71A57N0500D	-
71A57A2500D	-
71A55A3500D	-
71A5593001D	-
71A55A0500D	-

order code	Housing
71A55A0600	-
71A55A0610	-
71A5741001D	-
71A6041500D	-
71A60A1500DA	NA
71A60A2510DA	-

Core & Coil (71A) MH 175W - 450W

order code	Housing
71A57A0500D	-
71A5791500D	-
71A55A0001D	-
71A57A0001D	-
71A6071001D	-
71A60A1001D	-
71A5570001D	-
71A5692001D	-
71A56A2500D	-
71A5770001D	-
71A5771001D	-
71A5892001D	-
71A5993001D	-
71A6041001D	-
71A6092001D	-
71A60E6500	-
71A61E6500D	-
71A5540001D	-
71A60N1500	-
71A5590500D	-
71A5541500DTEE	-
71A55H0500DML	-
71A57H0500DMLA	-
71A60H1500DMLA	-
71A6052001D	-
71A5792500DXEE	-
AS205W480T500DEE	NA
AS205WQUAD500DEE	-
71A5752001D	-
71A6042001D	-
71A5750001D	-
71A5792001D	-
71A6051001D	-
71A57N2500D	-
71A58N2500D	-
71A60N2500D	-
71A5590510D	-
71A58N2510D	-
71A6091510DA	-
71A5590500DML	-
71A5593500DML	-
71A5790500DA	-
71A5892500DMLA	-
71A6091500DA	-
71A6091500DMLA	-
71A58A2500DA	-
71A59A3500DA	-
71A60A2500DA	-

order code	Housing
71A60A1600A	-
71A5842001DT	-
71A60A2600A	-
71A5792500DMLA	-
71A57A0600A	-
71A6041500DMLA	-
71A6092500DMLA	-
71A5790500DMLA	-
71A5593500DEE	-
71A5591500DEE	-
71A5543500DTEE	-
71A5692500DEE	-
71A5642500DTEE	-
71A5742500DTEE	-
71A5792500DEE	-
71A5842500DTAEE	-
71A5892500DAEE	-
71A5943500DTAEE	-
71A5993500DAEE	-
71A5892510DAEE	-
71A5892600AEE	-
71A5842510DTAEE	-
71A5993510DAEE	-
71A5993600AEE	-
71A5943600TAEE	-
71A6092500DAEE	-
71A6092510DAEE	-
71A6092600AEE	-
71A6042510DTAEE	-
71A6042600TAEE	-
71A5593600EE	-
71A5692510DEE	-
71A5742510DTEE	-
71A5792510DEE	-
71A5792600EE	-
71A5543600TEE	-
71A5593510DEE	-
71A6052500DAEE	-
71A5792520DEE	NA
71A5742520DTEE	-
71A5852500DAEE	-
71A5953500DAEE	-
71A5752500DAEE	-
71A5692520DEE	NA
71A5742600TEE	-
71A6393500DEE	-
71A6052600AEE	-
71A6343500DTEE	-

Core & Coil (71A) MH 175W - 450W

