



ROUND "COMBO" MACHINE SCREWS

SLOTTED AND PHILLIPS. STEEL ZINC CHROMATE

In 1985, Metallics was the first fastener company in America to offer a full line of Combo's!



STOCK NO.	UPC NO.	DIAMETER	LENGTH	WT. PER PKG.	STD. PKG/ MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER
JRM17	80023	6-32	3/8	.25	100/500	2.98/c
JRM80	80024	6-32	1/2	.27	100/500	3.28/c
JRM81	80025	6-32	3/4	.34	100/500	3.18/c
JRM63	80026	6-32	1	.42	100/500	3.53/c
JRM68	80027	6-32	1 1/4	.49	100/500	3.85/c
JRM82	80028	6-32	1 1/2	.56	100/500	4.78/c
JRM83	80029	6-32	2	.70	100/500	6.90/c
JRM140	80030	6-32	2 1/2	.86	100/500	7.23/c
JRM142	80031	6-32	3	1.02	100	8.38/c
JRM144	81129	6-32	4	1.41	100	25.45/c NEW
JRM18	80032	8-32	3/8	.34	100/500	2.98/c
JRM84	80033	8-32	1/2	.40	100/500	3.33/c
JRM85	80034	8-32	3/4	.51	100/500	3.55/c
JRM86	80035	8-32	1	.60	100/500	4.00/c
JRM87	80036	8-32	1 1/4	.73	100/500	4.50/c
JRM88	80037	8-32	1 1/2	.83	100/500	5.30/c
JRM89	80038	8-32	2	1.08	100/500	7.40/c
JRM90	80039	8-32	2 1/2	1.27	100/500	8.03/c
JRM91	80040	8-32	3	1.58	100	9.33/c
JRM23	81085	8-32	4	2.01	100	13.03/c NEW
JRM19	80041	10-24	3/8	.45	100/500	3.38/c
JRM32	80042	10-24	1/2	.52	100/500	3.40/c
JRM92	80043	10-24	3/4	.67	100/500	4.03/c
JRM93	80044	10-24	1	.81	100/500	4.55/c
JRM94	80045	10-24	1 1/4	.95	100/500	5.03/c
JRM95	80046	10-24	1 1/2	1.12	100/500	5.88/c
JRM96	80047	10-24	2	1.39	100/500	7.40/c
JRM97	80048	10-24	2 1/2	1.65	100	8.93/c
JRM127	80049	10-24	3	1.97	100	10.40/c
JRM150	86150	10-24	4	2.57	100	23.53/c NEW
JRM20	80050	10-32	3/8	.48	100/500	3.38/c
JRM33	80051	10-32	1/2	.55	100/500	3.40/c
JRM48	80052	10-32	3/4	.70	100/500	4.03/c
JRM98	80053	10-32	1	.86	100/500	4.55/c
JRM69	80054	10-32	1 1/4	.99	100/500	5.03/c
JRM75	80055	10-32	1 1/2	1.14	100/500	5.88/c
JRM113	80056	10-32	2	1.47	100/500	7.40/c
JRM114	86114	10-32	2 1/2	1.79	100	8.23/c NEW
JRM190	86190	10-32	3	2.11	100	13.93/c NEW
JRM22	80057	1/4-20	3/8	.90	100/500	5.88/c
JRM99	80058	1/4-20	1/2	1.00	100/500	6.23/c
JRM100	80060	1/4-20	3/4	1.25	100/500	6.90/c
JRM101	80061	1/4-20	1	1.54	100/500	7.88/c
JRM102	80062	1/4-20	1 1/4	1.78	100/500	8.03/c
JRM103	80063	1/4-20	1 1/2	2.00	100/500	8.15/c
JRM104	80064	1/4-20	2	2.52	100	11.00/c
JRM105	81105	1/4-20	2 1/2	3.06	100	13.93/c
JRM128	81110	1/4-20	3	3.58	100	14.60/c
JRM132	81115	1/4-20	4	4.61	100	18.85/c
JRM133	81116	1/4-20	5	5.95	100	36.93/c NEW
JRM134	81119	1/4-20	6	6.77	100	67.18/c NEW

CONTINUED ON NEXT PAGE