

WISTEN



P4436-20



The Wisten Collection features sweeping arcs framing elegant, tapered glass shades. Cool and modern with a casual flair, Wisten provides a signature universal look to any room.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO AVAILABLE IN

- Bath & Vanity
- Close-to-ceiling
- Fan Light Kit

PAIR WITH

Ratio

WALL BRACKET

P2794-20 Antique Bronze
4-1/2" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT FOYER

P3509-20 Antique Bronze
12" dia., 25-7/8" ht.
Overall ht. w/chain 101"; wire 15'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT INVERTED PENDANT

P3757-20 Antique Bronze
18-1/4" dia., 25" ht.
Overall ht. w/chain 100"; wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4434-20 Antique Bronze
17" dia., 20-1/2" ht.
Overall ht. w/chain 96"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P4435-20 Antique Bronze
35" L., 12-1/2" W., 29" ht.
Overall ht. w/stem 79"; wire 15'.
Four candelabra base lamps,
each 60w max

FIVE-LIGHT CHANDELIER

P4436-20 Antique Bronze
22" dia., 26-3/8" ht.
Overall ht. w/chain 101"; wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P4439-20 Antique Bronze
Two-tier.
27" dia., 33-3/8" ht.
Overall ht. w/chain 156"; wire 15'.
Nine candelabra base lamps,
each 60w max.

MINI-PENDANT

P5108-20 Antique Bronze
4" dia., 6-3/4" ht.
Overall ht. w/stem 64"; wire 10'.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT

P5112-20 Antique Bronze
17" dia., 21-1/8" ht.
Overall ht. w/chain 97"; wire 15'.
One medium base lamp,
100w max.

MINI-PENDANT

P5167-20 Antique Bronze
3-3/4" dia., 9-3/4" ht.
Overall ht. w/stem 67"; wire 10'.
One medium base lamp,
100w max.



P4434-20



P3509-20



P5167-20



P3757-20



P4435-20



P5108-20



P5112-20



P4439-20



P2794-20



P4436-09



P5167-09



P5108-09
P5108-09EBWB

MINI-PENDANT
P5108-09 Brushed Nickel
 4" dia., 6-3/4" ht.
 Overall ht. w/stem 64"; wire 10'.
 One medium base lamp, 100w max.

CFL MINI-PENDANT
P5108-09EBWB Brushed Nickel
 4" dia., 6-3/4" ht.
 Overall ht. w/stem 64"; wire 10'.
 One 13w GU24 CFL lamp, included.



WISTEN

WALL BRACKET
P2794-09 Brushed Nickel
 4-1/2" W., 8-1/4" ht.
 Extends 6-1/4". H/CTR 4".
 One medium base lamp,
 100w max.

THREE-LIGHT FOYER
P3509-09 Brushed Nickel
 12" dia., 25-7/8" ht.
 Overall ht. w/chain 101"; wire 15'.
 Three candelabra base lamps,
 each 60w max.

THREE-LIGHT INVERTED PENDANT
P3757-09 Brushed Nickel
 18-1/4" dia., 25" ht.
 Overall ht. w/chain 100"; wire 15'.
 Three medium base lamps,
 each 100w max.

THREE-LIGHT CHANDELIER
P4434-09 Brushed Nickel
 17" dia., 20-1/2" ht.
 Overall ht. w/chain 96"; wire 15'.
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT LINEAR CHANDELIER
P4435-09 Brushed Nickel
 35" L., 12-1/2" W., 29" ht.
 Overall ht. w/stem 79"; wire 15'.
 Four candelabra base lamps,
 each 60w max.

FIVE-LIGHT CHANDELIER
P4436-09 Brushed Nickel
 22" dia., 26-3/8" ht.
 Overall ht. w/chain 101"; wire 15'.
 Five candelabra base lamps,
 each 60w max.

NINE-LIGHT CHANDELIER
P4439-09 Brushed Nickel
 Two-tier.
 27" dia., 33-3/8" ht.
 Overall ht. w/chain 156"; wire 15'.
 Nine candelabra base lamps,
 each 60w max.

ONE-LIGHT PENDANT
P5112-09 Brushed Nickel
 17" dia., 21-1/8" ht.
 Overall ht. w/chain 97"; wire 15'.
 One medium base lamp,
 100w max.

MINI-PENDANT
P5167-09 Brushed Nickel
 3-3/4" dia., 9-3/4" ht.
 Overall ht. w/stem 67"; wire 10'.
 One medium base lamp,
 100w max.



P4434-09



P3509-09



P3757-09



P4435-09



P5112-09



P4439-09



P2794-09

WISTEN

Simple, modern and elegant, the Wisten family features a sculptured linear look. Etched glass for soft contemporary feel.

FINISHES

● Brushed Nickel - 09

● Antique Bronze - 20

ALSO AVAILABLE IN

Fixture Collections

Close-to-Ceiling

ONE-LIGHT BATH

P2794-09 Brushed Nickel

P2794-20 Antique Bronze

4-1/2" W., 8-1/4" ht.

Extends 6-1/4".

One medium base lamp, 100w max.

TWO-LIGHT BATH

P2795-09 Brushed Nickel

P2795-20 Antique Bronze

12-1/2" W., 8-1/4" ht.

Extends 6-1/4".

Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2796-09 Brushed Nickel

P2796-20 Antique Bronze

21" W., 8-1/4" ht.

Extends 6-1/4".

Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2797-09 Brushed Nickel

P2797-20 Antique Bronze

29-1/2" W., 8-1/4" ht.

Extends 6-1/4".

Four medium base lamps, each 100w max.



P2794-20

P2795-20



P2796-09



P2796-20



P2797-09



P2797-20



P2794-09

P2795-09



P2794-09
mounted down

P2795-09
mounted down

Shown: P2797-09 bath fixture



WISTEN

Wisten's domed glass offers a simple, modern and elegant touch.



P3290-09
P3290-09EBWB



P3290-20

TWO-LIGHT FLUSH MOUNT

P3290-09 Brushed Nickel

P3290-20 Antique Bronze
14" dia., 7" ht.

Two medium base lamps,
each 100w max.

TWO-LIGHT CFL FLUSH MOUNT

P3290-09EBWB Brushed Nickel

14" dia., 7" ht.

Two 13w GU24 CFL lamps, included.



WISTEN

Universal-style light kit with quick-connect wiring.

P2649-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
11" dia., 6-1/4" ht.
Two medium base 10w, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimnable)



Dry
Indoor only



P2649-01WB
Shown with
-09 finial



P2649-01WB
Shown with
-20 finial

WISTEN

Simple, modern and elegant, the Wisten family features a sculptured linear look. Etched glass for soft contemporary feel.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ONE-LIGHT

P3360-09 Brushed Nickel
P3360-20 Antique Bronze
Wall or ceiling mount.
5-1/4" W., 8-1/2" ht.
One 18w GU24 CFL lamp.



P3360-09



P3361-09

THREE-LIGHT

P3361-09 Brushed Nickel
P3361-20 Antique Bronze
Wall or ceiling mount.
11" W. canopy, 8-1/4" ht.
Three 18w GU24 CFL lamps.



P3363-09



P3362-09

FOUR-LIGHT

P3362-09 Brushed Nickel
P3362-20 Antique Bronze
Wall or ceiling mount.
40" W., 9" ht.
Four 18w GU24 CFL lamps.



P3360-20



P3361-20

THREE-LIGHT

P3363-09 Brushed Nickel
P3363-20 Antique Bronze
Wall or ceiling mount.
26" W., 9" ht.
Three 18w GU24 CFL lamps.



P3363-20



P3362-20